






- 技术要求:
1. 塑件材料:PA66 (UL-94V-0)
 2. 接触件: 黄铜镀锡
 3. 接触电阻: $\leq 10m\Omega$
 4. 绝缘电阻: $\geq 100M\Omega$
 5. 额定电压: 250V AC DC
 6. 额定电流: 2.0A AC DC
 7. 耐压: 能承受1000V AC/Minute
 8. 工作温度: $-25^{\circ}\sim +85^{\circ}$
 9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 235^{+5}_{-0} , 时间 2.5 ± 0.5 秒
 10. 铅和镉等六大有害物质含量要符合环保要求.

PIN number variable size comparison table				
PART NO	PIN	A	W	C
WF-ZH1.5-2PWZ	2	1.50	3.60	4.50
WF-ZH1.5-3PWZ	3	3.00	5.10	6.00
WF-ZH1.5-4PWZ	4	4.50	6.60	7.50
WF-ZH1.5-5PWZ	5	6.00	8.10	9.00
WF-ZH1.5-6PWZ	6	7.50	9.60	10.50
.....				
WF-ZH1.5-16PWZ	16	22.50	24.60	25.50



2	端子 Contact	黄铜	N*1	电镀(锡):整个表面 镀底镍30u~MIN, 再镀锡80u~MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.X ±0.30	X.° ±5°	PART NO. WF-ZH1.5-NPWZ	TITLE: ZH1.5MM 弯针	
.XX ±0.20	X.X° ±1°			
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE A4
MANUFACTURE DWG		CHED: Talen		UNITS MM
		APPD: Sophia		SCALE N:A
				SHEET 1/1