

1.Description

The UMW SN74LVC1G04 is a non gate integrated circuit, which can realize the mathematical logic operation of $Y=A$. It is designed with advanced CMOS technology, which has the characteristics of low power consumption and high output driving ability. The chip can work normally when the voltage of V_{CC} is between 1.65V and 5.5V. And 74lvc1g04 has a variety of small package shapes, which can be widely used in high-end precision instruments, miniaturized low-power handheld devices, and artificial intelligence and other fields.


2.Features

- Low input current: typical value 0.1 μ A
- Low static power consumption: typical value 0.1 μ A
- High output: $V_{CC}=4.5V$, greater than 32mA
- Wide operating voltage range: 1.65V to 5.5V
- Package form: SOT23-5/SC70-5/SOT-553 DFN/SON-6, DSBGA-5, X2SON-5

3.Product Use

- Portable audio interface
- digital television
- Wireless headphones, smart watches, etc.
- Blu-ray player and home theater
- Solid state drive
- Smart wearable devices

4.Pinning information





5.Pin Function

Name	Pin				Explain
	SOT23-5/SC70-5/SOT-553	DFN/SON-6	DSBGA-5	X2SON-5	
NC	1	1,5	A1, B2	1	Empty Feet
A	2	2	B1	2	Input
GND	3	3	C1	3	Power Ground
Y	4	4	C2	4	Output
V _{CC}	5	6	A2	5	Power Supply Positive

Notes: NC -- Empty feet, no internal connection line.

6.Limit Parameter


Parameter	Symbol	Limit Value	Unit
Working Voltage	V _{CC}	6.5	V
Input	V _{IN}	-0.5 ~ 6.5	V
Output Voltage (1)	V _{OUT}	-0.5 ~ 6.5	V
Single Pin Output Current	I _{OUT}	25	mA
VCC or Gnd Current	I _{CC}	50	mA
Storage Temperature	T _S	-65 to 150	°C
Pin Welding Temperature	T _W	260, 10s	°C
Working Temperature	T _A	-40 to 105	°C

Note:

1. When VCC=0V, the limit voltage that the output can withstand.
2. The limit value of any parameter can not be exceeded.If the limit value is exceeded, it may cause physical damage such as product deterioration;At the same time, the chip can not be guaranteed to work normally when it is close to the limit parameters.



7.Principle Logic Diagram



Function Table

Input	Output
A	Y
L	H
H	L



8. Electrical Characteristics


Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Working Voltage	V_{CC}		1.65		5.5	V
Input High Level Voltage	V_{IH}	$V_C=1.65V\sim1.95V$	$0.65*V_{CC}$			V
		$V_C=2.3V\sim2.7V$	1.7			V
		$V_C=3V\sim5.5V$	$0.7*V_{CC}$			V
Low-level Input Voltage	V_{IL}	$V_C=1.65V\sim1.95V$			$0.35*V_{CC}$	V
		$V_C=2.3V\sim2.7V$			0.7	V
		$V_C=3V\sim5.5V$			$0.3*V_{CC}$	V
Input Voltage	V_I				5.5	V
Output Voltage	V_O				V_{CC}	V
High Level Output Current	I_{OH}	$V_C=1.65V$			-4	mA
		$V_C=2.3V$			-8	mA
		$V_C=3V$			-16	mA
		$V_C=4.5V$			-32	mA
Low Level Output Current	I_{OL}	$V_C=1.65V$			4	mA
		$V_C=2.3V$			8	mA
		$V_C=3V$			16	mA
		$V_C=4.5V$			32	mA
High Level Load Voltage	V_{OH}	$I_{OH}=-100\mu A, V_{CC}=1.65\sim5.5V$	$V_{CC}-0.1$			V
		$I_{OH}=-4mA, V_{CC}=1.65V$	1.2			V
		$I_{OH}=-8mA, V_{CC}=2.3V$	1.9			V
		$I_{OH}=-16mA, V_{CC}=3V$	2.4			V
		$I_{OH}=-32mA, V_{CC}=4.5V$	3.8			V
Low Level Load Voltage	V_{OL}	$I_{OH}=100\mu A, V_{CC}=1.65\sim5.5V$			0.1	V
		$I_{OH}=4mA, V_{CC}=1.65V$			0.45	V
		$I_{OH}=8mA, V_{CC}=2.3V$			0.3	V
		$I_{OH}=16mA, V_{CC}=3V$			0.4	V
		$I_{OH}=32mA, V_{CC}=4.5V$			0.55	V



Parameter	Symbol		Conditions	Min.	Typ.	Max.	Unit
Input Current	I_i	A	$V_i=5.5V$ or GND	0~5.5V	0.1	5	μA
Turn-off Current	I_{OFF}	V_i	$V_i=5.5V$	0	0.1	10	μA
		V_o	$V_o=5.5V$	0	0.1	10	μA
Working current	I_{CC}		$V_i=5.5V, I_o=0$	1.65V~5.5V	0.1	10	μA
			$V_i=GND, I_o=0$		0.1	10	μA
Working Current Variation	ΔI_{CC}		$A=V_{CC}-0.6V$	3V~5.5V	25	-	μA

$T_A=25^{\circ}C$, $V_{CC}=5.0V$, $T_R \leq 20ns$. See test method.

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Maximum transmission delay time a, B to Y	t_{PHL}	$C=15pF$		10		ns
	t_{PLH}			10		ns




Note: 1. CL capacitor is external chip capacitor (0603), which is connected close to the output pin, and the capacitor ground is close to the chip GND;

2. Input: port input level, $f=500\text{kHz}$, $D=50\%$; $t_r=t_f \leq 20\text{ns}$;

3. Output: y-end output test.



9.1 SOT23-5 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E1	E	e	e1	L	θ
Min	1.050	0.000	1.050	0.300	0.100	2.820	1.500	2.650	0.950	1.800	0.300	0°
Max	1.250	0.100	1.150	0.500	0.200	3.020	1.700	2.950	BSC	2.000	0.600	8°



9.2 SC70-5 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1	L	θ
Min	0.90	0.00	0.90	0.15	0.08	2.05	1.15	2.15	0.65	1.20	0.26	7°
Max	1.10	0.10	1.00	0.35	0.15	2.25	1.35	2.45	TYP	1.40	0.46	REF.



9.3 SON-6 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1
Min	0.95	0.95	-	0.7	0.35	0.1	0.35	0.12	0.11	0.00
Max	1.05	1.05	0.4				0.45	0.22	TYP	0.05



9.4 DFN(1*1.5) Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1	L	H
Min	0.95	1.4	1	0.5	0.6	0.05	0.3	0.25	0.15	-	0.00	0.127
Max	1.05	1.5				TYP	0.4	0.35	0.25	0.6	0.05	TYP



9.5 DSBGA-5 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	B	C
Min	0.5	-	0.05
Max	TYP	0.05	-



9.6 X2SON-5 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1	L	L1
Min	0.75	-	0.05	0.48	0.17	0.06	0.25	0.23	0.15	0.26	0.17	0.1
Max	0.85	0.4			0.27			0.32	0.35		0.27	

Symbol	H
Min	0.00
Max	0.05



9.7 SOT-553 Package Outline Dimensions



DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1
Min	1.50	1.10	0.13	1.50	0.50	0.15	0.20	0.50	0.00	0.08
Max	1.70	1.30	0.27	1.70		0.25	0.40	0.60	0.05	0.18



10.Ordering information



yww: Batch Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW SN74LVC1G04DBVR	C04F	SOT23-5	3000	Tape and reel
UMW SN74LVC1G04DCKR	CCF	SC70-5	3000	Tape and reel
UMW SN74LVC1G04DSFR	CC	DFN(1*1)	10000	Tape and reel
UMW SN74LVC1G04DRYR	CC	DFN(1*1.5)	5000	Tape and reel
UMW SN74LVC1G04YZPR	CC7	DSBGA-5	3000	Tape and reel
UMW SN74LVC1G04DPWR	K4	X2SON-5	3000	Tape and reel
UMW SN74LVC1G04DRLR	CC7	SOT-553	4000	Tape and reel



11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.