






Technical requirements	
Characteristic impedance	50Ω
Frequency range	0-6GHZ
Contact resistance	
Inner conductor	≤3mΩ
Outer conductor	≤2mΩ
Insulated resistance	≥5000MΩ
Salt spray time	48H
Separation force	≥0.28N
Appearance: no shift point burr scratch surface bright, no dirt, no deformation, etc	



PCB WELDING DRAWING (TOLERANCE: ±0.05)

1	半螺铜套	1	黄铜	镀金
2	母针	1	黄铜	镀金
3	绝缘体 1	1	PTFE	
4	铜座	1	黄铜	
5	绝缘体 2	1	PTFE	
序号	名称	数量	材料	备注

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
.X±0.30	X.°±5°	PART NO.	TITLE:	
.XX±0.25	X.X°±1°	HMT-SMA-K513-KWE	弯头-半螺内孔-H13*14.5-LW	
.XXX±0.15		DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		SCALE
				SHEET
				N:A
				1/1