

1.Description

The small size and low power consumption (34 μ A per channel maximum) of the OPA347 make it ideal for portable and battery-powered applications.

The input range of the UMW OPA347 extends 200 mV beyond the rails, and the output range is within 5mV of the rails. The UMW OPA347 also features an excellent speed/power ratio with a bandwidth of 350kHz.

The UMW OPA347 can be operated with a single or dual power supply from 2.3V to 5.5V. All models are specified for operation from -55°C to $+125^{\circ}\text{C}$.


2.Features

- Low I_Q : 20 μ A
- High Speed/power Ratio With
- Bandwidth: 350kHz
- Rail-to-rail Input And Output
- Single Supply: 2.3V to 5.5V


3.Applications

- Portable Equipment
- Battery-powered Equipment
- 2-wire Transmitters
- Smoke Detectors
- Co Detectors


4.Pinning Information



**OPA347
SC70-5**



**OPA2347
SOP-8**



**OPA4347
TSSOP-14/SOP-14**



5. Absolute Maximum Ratings

Parameter	Value
Supply Voltage: $V^+ - V^-$	7.5V
Signal Input Terminals, Voltage	$(V^-) - 0.5V$ to $(V^+) + 0.5V$
Current	10mA
Output Short-Circuit	Continuous
Operating Temperature	-65°C to 150°C
Storage Temperature	-65°C to 150°C
Junction Temperature	150°C



6. Electrical Characteristics: $V_S=2.5V$ to $5.5V$

Boldface limits apply over the specified temperature range, $T_A=-55^{\circ}C$ to $+125^{\circ}C$.

At $T_A=+25^{\circ}C$ and $R_L=100k\Omega$ connected to $V_S/2$ $V_{OUT}=V_S/2$, unless otherwise noted.

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Input Offset Voltage	V_{OS}	$V_S=5.5V$, $V_{CM}=(V_-)+0.8V$		2	6	mV
over Temperature				2	7	mV
Drift	dV_{OS}/dT			3		$\mu V/^{\circ}C$
vs Power Supply	PSRR	$V_S=2.5V$ to $5.5V$, $V_{CM}<(V_+)-1.7V$		60	175	$\mu V/V$
Over Temperature		$V_S=2.5V$ to $5.5V$, $V_{CM}<(V_+)-1.7V$			300	$\mu V/V$
Channel Separation, DC				0.3		$\mu V/V$
		$f=1kHz$		128		dB
Common-Mode Voltage Range	V_{CM}		$(V_-)-0.2$		$(V_+)+0.2$	V
Common-Mode Rejection Ratio	CMRR	$V_S=5.5V$, $(V_-)-0.2V < V_{CM} < (V_+)-1.7V$	70	80		dB
Over Temperature		$V_S=5.5V$, $V_- < V_{CM} < (V_+)-1.7V$	66			dB
		$V_S=5.5V$, $(V_-)-0.2V < V_{CM} < (V_+)+0.2V$	54	70		dB
Over Temperature		$V_S=5.5V$, $V_- < V_{CM} < V_+$	48			dB
Input Bias Current	I_B			± 0.5	± 10	pA
Input Offset Current	I_{OS}			± 0.5	± 10	pA
Differential				$10^{13} 3$		ΩpF
Common-Mode				$10^{13} 6$		ΩpF
Noise		$V_{CM} < (V_+) - 1.7V$				
Input Voltage Noise, $f=0.1Hz$ to $10Hz$				12		μV_{PP}
Input Voltage Noise Density, $f=1kHz$	e_n			60		$nV/\sqrt{Hz}$
Input Current Noise Density, $f=1kHz$	i_n			0.7		$fA/\sqrt{Hz}$
Open-Loop Voltage Gain	A_{OL}	$V_S=5.5V$, $R_L=100k\Omega$ $0.015V < V_O < 5.485V$	100	115		dB



Parameter	Symbol	Conditions	Min	Typ	Max	Units
over Temperature		$V_S=5.5V$, $R_L=100k\Omega$ $0.015V < V_O < 5.485V$	88			dB
		$V_S=5.5V$, $R_L=5k\Omega$ $0.125V < V_O < 5.375V$	100	115		dB
over Temperature (SC-70 only)	A_{OL}	$V_S=5.5V$, $R_L=5k\Omega$	88			dB
		$0.125V < V_O < 5.375V$	96	115		dB
Voltage Output Swing from Rail		$R_L=100k\Omega$, $A_{OL}>100dB$		5	15	mV
over Temperature		$R_L=100k\Omega$, $A_{OL}>88dB$			15	mV
		$R_L=5k\Omega$, $A_{OL}>100dB$		90	125	mV
over Temperature		$R_L=5k\Omega$, $A_{OL}>88dB$			125	mV
Short-Circuit Current	I_{SC}			± 17		mA
Capacitive Load Drive	C_{LOAD}		See Typical Characteristics			
Frequency Response		$C_L=100pF$				
Gain-Bandwidth Product	GBW			350		kHz
Slew Rate	SR	$G=+1$		0.17		V/ μs
Settling Time, 0.1%	t_s	$V_S=5V$, 2V Step, $G=+1$		21		μs
0.01%		$V_S=5V$, 2V Step, $G=+1$		27		μs
Overload Recovery Time		$V_{IN} \times \text{Gain} = V_S$		23		μs
Specified Voltage Range	V_S		2.5		5.5	V
Minimum Operating Voltage				2.3		V
Minimum Operating Voltage (OPA347SA)				2.4		V
Quiescent Current (per amplifier)	I_Q	$I_O=0$		20	34	μA
over Temperature					38	μA



Parameter	Symbol	Conditions	Min	Typ	Max	Units
Specified Range			-55		125	°C
Operating Range			-65		150	°C
Storage Range			-65		150	°C
Thermal Resistance	θ_{JA}					
SOT23-5 Surface-Mount				200		°C/W
SOT23-8 Surface-Mount				150		°C/W
SO-8 Surface-Mount				150		°C/W
SO-14 Surface-Mount				100		°C/W
TSSOP-14 Surface-Mount				100		°C/W
DIP-8				100		°C/W
SC70-5 Surface-Mount				250		°C/W
WCSP				250		°C/W



7.1 Typical characteristic




Figure 1: Open-loop Gain/phase vs Frequency




Figure 2: Power-supply Rejection Ratio And Common-mode Rejection Ratio vs Frequency




Figure 3: Maximum Output Voltage vs Frequency




Figure 4: Channel Separation vs Frequency




Figure 5: Quiescent And Short-circuit Current vs Supply Voltage




Figure 6: Output Voltage Swing vs Output Current



7.2 Typical characteristic




Figure 7: Common-mode Rejection vs Temperature




Figure 8: Open-loop Gain And Power-supply Rejection vs Temperature




Figure 9: Quiescent And Short-circuit Current vs Temperature




Figure 10: Input Bias Current vs Temperature




Figure 11: Offset Voltage Production Distribution




Figure 12: Offset Voltage Drift Magnitude Production Distribution



7.3 Typical characteristic




Figure 13: Small-signal Overshoot vs Load Capacitance




Figure 14: Small-signal Overshoot vs Load Capacitance




Figure 15: Small-signal Step Response
 $G=+1V/V$, $R_L=100k\Omega$, $C_L=100pF$




Figure 16: Small-signal Step Response
 $G=+1V/V$, $R_L=5k\Omega$, $C_L=100pF$




Figure 17: Large-signal Step Response
 $G = +1V/V$, $R_L=100k\Omega$, $C_L=100pF$





Figure 18: Input Voltage And Current Noise Spectral Density vs Frequency



8.1 SC70-5 (SOT353) Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1	L	θ
Min	0.90	0.00	0.90	0.15	0.08	2.05	1.15	2.15	0.65	1.20	0.26	7°
Max	1.10	0.10	1.00	0.35	0.15	2.25	1.35	2.45	TYP	1.40	0.46	REF.



8.2 SOP-14 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	A3	b	C	D	E	E1	e	h	L
Min	-	0.05	1.35	0.65	0.203	0.17	8.45	5.80	3.80	1.24	0.25	0.40
Max	1.75	0.25	1.55	0.75	0.305	0.25	8.85	6.20	4.00	1.30	0.50	0.80

Symbol	L1	θ
Min	1.00	0°
Max	1.10	8°



8.3 SOP-8 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	L	θ
Min	1.350	0.000	1.350	0.330	0.170	4.700	3.800	5.800	1.270	0.400	0°
Max	1.750	0.100	1.550	0.510	0.250	5.100	4.000	6.200	BSC	1.270	8°



8.4 TSSOP-14 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	b1	c	c1	D	E	E1	e	L1
Min	-	0.05	0.90	0.20	0.19	0.13	0.120	4.90	6.20	4.30	0.65	0.85
Max	1.20	0.15	1.05	0.28	0.25	0.17	0.14	5.10	6.60	4.50	BSC	1.15

Symbol	L	θ
Min	0.45	0°
Max	0.75	8°



9.Ordering information



Order Code	Marking	Package	Base QTY	Delivery Mode
UMW OPA347SA	S47	SC70-5	3000	Tape and reel
UMW OPA4347UA	OPA4347UA	SOP-14	2500	Tape and reel
UMW OPA2347UA	OPA2347UA	SOP-8	2500	Tape and reel
UMW OPA4347EA	OPA4347EA	TSSOP-14	4000	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.