

1.Description


The UMW SN74LVC2G14 is a high performance dual inverter with Schmitt-Trigger inputs operating from a 1.65 to 5.5 V supply. Pin configuration and function are the same as the UMW SN74LVC2G04, but the inputs have hysteresis and, with its Schmitt trigger function, the UMW SN74LVC2G14 can be used as a line receiver which will receive slow input signals.

The UMW SN74LVC2G14 is capable of transforming slowly changing input signals into sharply defined, jitter-free output signals. In addition, it has a greater noise margin than conventional inverters.

2.Features

- Designed for 1.65V to 5.5V V_{CC} Operation
- Over Voltage Tolerant Inputs and Outputs
- LVTTTL Compatible – Interface Capability with 5V TTL Logic with $V_{CC}=3V$
- LVCMOS Compatible
- 24 mA Balanced Output Sink and Source Capability
- Near Zero Static Supply Current Substantially Reduces System Power Requirements
- Current Drive Capability is 24 mA at the Outputs
- Chip Complexity: FET=72
- These Devices are Pb-Free and are RoHS Compliant

3.Pinning information



SOT23-6/SC70-6

Figure1. Top View



4.Pin Function

Pin	Function
1	INA1
2	GND
3	INA2
4	$\overline{Y2}$
5	VCC
6	$\overline{Y1}$

5.Block Diagram




Figure2. Logic Symbol

Function Table

Input	Output
A	Y
L	H
H	L



6. Absolute Maximum Ratings

Parameter	Symbol	Value	Units
DC Supply Voltage	V_{CC}	-0.5 to 7	V
DC Input Voltage	V_I	$-0.5 \leq V_I \leq 7$	V
DC Output Voltage Output in Higher or Low State (Note 1)	V_O	-0.5 to $V_{CC} + 0.5$	V
DC Input Diode Current $V_I < GND$	I_{IK}	-50	mA
DC Output Diode Current $V_O < GND, V_O > V_{CC}$	I_{OK}	± 50	mA
DC Output Sink Current	I_O	± 50	mA
DC Supply Current per Supply Pin	I_{CC}	± 100	mA
Storage Temperature Range	T_{STG}	-65 to 150	°C
Lead Temperature, 1 mm from Case for 10 Seconds	T_L	260	°C
Junction Temperature Under Bias	T_J	150	°C
Thermal Resistance	θ_{JA}	333	°C/W
Power Dissipation in Still Air at 85°C	P_D	200	mW
Moisture Sensitivity	MSL	Level 1	
Flammability Rating Oxygen Index: 28 to 34	F_R	UL94V-0@0.12in	
ESD Classification Human	Body Model (Note 2)	2000	V
	Machine Model (Note 3)	200	V
	Charged Device Model (Note 4)	N/A	V
Latchup Performance Above V_{CC} and Below GND at 125°C (Note 5)	$I_{Latchup}$	± 100	mA

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. IO absolute maximum rating must be observed.
2. Tested to EIA/JESD22—A114—A, rated to EIA/JESD22—A114—B.
3. Tested to EIA/JESD22—A115—A, rated to EIA/JESD22—A115—A.
4. Tested to JESD22—C101—A.
5. Tested to EIA/JESD78.



7.Recommended Operating Conditions

Parameter	Symbol	Min	Max	Unit
DC Supply Voltage Operating	V_{CC}	1.65	5.5	V
Data Retention		1.5	5.5	V
DC Input Voltage	V_{IN}	0	5.5	V
DC Output Voltage (High or Low State)	V_{OUT}	0	5.5	V
Operating Temperature Range	T_A	-40	125	°C

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended.



8.DC Electrical Characteristics

Parameter	Condition	Symbol	$V_{CC}(V)$	$T_A=25^{\circ}C$			$-40^{\circ}C \leq T_A \leq 125^{\circ}C$		Units
				Min	Typ	Max	Min	Max	
Positive-going Input Threshold Voltage		V_{T+}	1.65	0.7		1.4	0.7	1.4	V
			2.3	1		1.7	1	1.7	
			3	1.3		2.2	1.3	2.2	
			4.5	1.9		3.1	1.9	3.1	
			5.5	2.2		3.7	2.2	3.7	
Negative-going Input Threshold Voltage		V_{T-}	1.65	0.3		0.7	0.3	0.7	V
			2.3	0.4		1	0.4	1	
			3	0.6		1.3	0.6	1.3	
			4.5	1.1		2	1.1	2	
			5.5	1.4		2.5	1.4	2.5	
Hysteresis ($V_{T+} - V_{T-}$)		ΔV_T	1.65	0.3		0.8	0.3	0.8	V
			2.3	0.4		0.9	0.4	0.9	
			3	0.4		1.1	0.4	1.1	
			4.5	0.6		1.3	0.6	1.3	
			5.5	0.7		1.4	0.7	1.4	
High-Level Output Voltage $V_{IN}=V_{IL}$	$I_{OH}=-100\mu A$	V_{OH}	1.65 to 5.5	$V_{CC}-0.1$	V_{CC}		$V_{CC}-0.1$		V
	$I_{OH}=-3mA$		1.65	1.29	1.52		1.29		
	$I_{OH}=-8mA$		2.3	1.9	2.1		1.9		
	$I_{OH}=-12mA$		2.7	2.2	2.4		2.2		
	$I_{OH}=-16mA$		3	2.4	2.7		2.4		
	$I_{OH}=-24mA$		3	2.3	2.5		2.3		
	$I_{OH}=-32mA$		4.5	3.8	4		3.8		



Parameter	Condition	Symbol	V _{CC} (V)	T _A =25°C			-40°C≤T _A ≤125°C		Units
				Min	Typ	Max	Min	Max	
Low-Level Output Voltage V _{IN} =V _{IH}	I _{OH} =100μA	V _{OL}	1.65 to 5.5		0.0	0.1		0.1	V
	I _{OL} =3mA		1.65		0.08	0.24		0.24	
	I _{OL} =8mA		2.3		0.2	0.3		0.3	
	I _{OL} =12mA		2.7		0.22	0.4		0.4	
	I _{OL} =16mA		3		0.28	0.4		0.4	
	I _{OL} =24mA		3		0.38	0.55		0.55	
	I _{OL} =32mA		4.5		0.42	0.55		0.55	
Input Leakage Current	V _{IN} =5.5V or GND	I _{IN}	0 to 5.5		±0.1			±1	μA
Power Off Leakage Current	V _{IN} =5.5V or V _{OUT} =5.5V	I _{OFF}	0			1		10	
Quiescent Supply Current	V _{IN} =5.5V or GND	I _{CC}	5.5			1		10	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.



9.AC Electrical Characteristics

Parameter	Condition	Symbol	V _{CC} (V)	T _A =25°C			-40°C≤T _A ≤125°C		Units
				Min	Typ	Max	Min	Max	
Propagation Delay (Figure 3 and 4)	R _L =1MΩ, C _L =15pF	t _{PLH} , t _{PHL}	1.65	2	5.3	11.4	2	12	ns
			1.8	2	4.4	9.5	2	10	
			2.5±0.2	0.2	3.5	6.5	0.8	4.1	
			3.3±0.3	0.8	2.1	4.5	0.5	3.7	
	R _L =500Ω, C _L =50pF		3.3±0.3	1.2	2.9	5.5	1.5	5.2	
	R _L =1MΩ, C _L =15pF		5.0±0.5	0.5	1.8	3.9	0.5	4.1	
	R _L =500Ω, C _L =50pF		5.0±0.5	0.8	2.4	4.3	0.8	4.5	

10.Capacitance Characteristics

Parameter	Symbol	Condition	Typ	Units
Input Capacitance	C _{IN}	V _{CC} =5.5V, V _I = 0V or V _{CC}	>2.5	pF
Power Dissipation Capacitance ⁽⁶⁾	C _{PD}	10MHz, V _{CC} =3.3V, V _I =0V or V _{CC}	4	pF
		10MHz, V _{CC} =5.5V, V _I =0V or V _{CC}	4	pF

Notes 6:

C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation: I_{CC(OPR)}=C_{PD}*V_{CC}*fin+I_{CC}*C_{PD} is used to determine the no-load dynamic power consumption; P_D=C_{PD}*V_{CC}²*fin+I_{CC}*V_{CC}*Fig.




Figure 3. switching Waveforms





Figure 4. Test Circuit



11.1 SC70-6 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1	L	L1
Min	0.90	0.00	0.90	0.15	0.08	2.05	2.15	1.15	0.65	1.2	0.26	0.525
Max	1.10	0.10	1.00	0.35	0.15	2.25	2.45	1.35	TYP.	1.4	0.46	REF.

Symbol	θ
Min	0°
Max	8°



11.2 SOT23-6 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E1	E	e	e1	L	θ
Min	1.050	0.000	1.050	0.300	0.100	2.820	1.500	2.650	0.950	1.800	0.300	0°
Max	1.250	0.100	1.150	0.500	0.200	3.020	1.700	2.950	BSC	2.000	0.600	8°



12.Ordering Information



yww: Batch Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW SN74LVC2G14DBVR	C145	SOT23-6	3000	Tape and reel
UMW SN74LVC2G14DCKR	CF5	SC70-6	3000	Tape and reel



13.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.