









PCB参考图



NO	Operating Type	Part No.
1	Push To Lock	PB-22E80L
2	Push No Lock	PB-22E80N

电路简示图

NOTE:
1.Operating Force: 300gf±50gf
2.Travel : 2.4±0.2mm



ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑧	Terminal	6	Brass strip	Plating silver
⑦	Contact	2	Phosphor bronze	Plating silver
⑥	Securing glue	2	POM	Black
⑤	Spring	1	SUS	Natural
④	Base	1	POM	Black
③	Crochet Needle	1	SUS	Natural
②	Cover	1	POM	White
①	KNOB	1	POM	Blue

APPROVALS	DATE
DRAWN G.M.Chen	2015/5/4

CHECKED	TITLE: PUSH SWITCH
APPROVALS	PART NO. PB-22E80X
TOLERANCES ARE	SCALE: 1:1
30 ^{±0.15}	ANGLE
10 ^{±0.20}	UNIT: mm
5 ^{±0.10}	DRAWING NO.
±2°	SHEET 1 OF 1
±0.10	PROJ.