




RoHS

VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table

PART NO	PIN	A	B	C
WF-PH2. 0-2PZZ	2	2.00	6.00	4.50
WF-PH2. 0-3PZZ	3	4.00	8.00	6.00
WF-PH2. 0-4PZZ	4	6.00	10.00	7.50
WF-PH2. 0-5PZZ	5	8.00	12.00	9.00
WF-PH2. 0-6PZZ	6	10.00	14.00	10.50
.....				
WF-PH2. 0-20PZZ	20	38.00	42.00	25.50

技术要求:

1. 塑件材料:PA66 (UL-94V-0)
2. 接触件:黄铜镀锡
3. 接触电阻: $\leq 10\text{m}\Omega$
4. 绝缘电阻: $\geq 100\text{M}\Omega$
5. 额定电压:250V AC DC
6. 额定电流:2.0A AC DC
7. 耐压:能承受1000V AC/Minute
8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
9. 可焊性试验:浸锡面积 $\geq 95\%$ 温度 235^{+5}_{-0} , 时间 2.5 ± 0.5 秒
10. 铅和铜等六大有害物质含量要符合环保要求.

SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

2	端子 Contact	黄铜	N*1	电镀(锡):整个表面 镀底镍 30u~MIN, 再镀锡 80u~MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO.	TITLE:	
.XX ±0.20	X.X* ±1°	WF-PH2.0-NPZZ	PH2.0MM 直针	
.XXX ±0.10	X.XX* ±0.5°	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		SCALE
				SHEET
				N:A 1/1