





RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table			
PART NO	PIN	A	B
WF-XH2. 54-2PWZ	2	2.50	7.50
WF-XH2. 54-3PWZ	3	5.00	10.00
WF-XH2. 54-4PWZ	4	7.50	12.50
WF-XH2. 54-5PWZ	5	10.00	15.00
WF-XH2. 54-6PWZ	6	12.50	17.50
.....			
WF-XH2. 54-20PWZ	20	47.50	52.50

- 技术要求:
1. 塑件材料:PA66 (UL-94V-0)
 2. 接触件:黄铜镀锡
 3. 接触电阻: $\leq 10m\Omega$
 4. 绝缘电阻: $\geq 100M\Omega$
 5. 额定电压:250V AC DC
 6. 额定电流:2.0A AC DC
 7. 耐压:能承受1000V AC/Minute
 8. 工作温度: $-25^{\circ} \sim +85^{\circ}$
 9. 可焊性试验:浸锡面积 $\geq 95\%$ 温度 235^{+5}_{-0} , 时间 2.5 ± 0.5 秒
 10. 铅和镉等六大有害物质含量要符合环保要求.

2	端子 Contact	黄铜	N*1	电镀(锡):整个表面镀底镍 30u~MIN, 再镀锡 80u~MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注



GENERAL TOLERANCES UNLESS SPECIFIED		深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.X	± 0.30	X.°	$\pm 5^{\circ}$	PART NO. WF-XH2.54-NPWZ
.XX	± 0.20	X.X°	$\pm 1^{\circ}$	TITLE: XH2.54MM 弯针
.XXX	± 0.10	X.XX°	$\pm 0.5^{\circ}$	DESIGN: James
MANUFACTURE DWG		CHEDED: Talen	CUSTOMER	
		APPD: Sophia		
				SIZE A4
				UNITS MM
				SCALE
				SHEET
				N:A 1/1