

P-Ch 100V Fast Switching MOSFETs
Applications


- High Frequency Switching and Synchronous Rectification.
- DC/DC Converters.
- Power Tool Application.

Features

- 100% EAS Guaranteed
- Green Device Available
- Fast Switching Speed
- Advanced high cell density SGT MOS Technology

Product Summary

V_{DS}	-100	V
$R_{DS(ON),typ}$	8.5	m Ω
I_D	-150	A

TOLL Pin Configuration

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	-100	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_C=25^\circ\text{C}$	Continuous Drain Current, V_{GS} @ -10V ¹	-150	A
$I_D@T_C=100^\circ\text{C}$	Continuous Drain Current, V_{GS} @ -10V ¹	-97	A
I_{DM}	Pulsed Drain Current ²	-600	A
EAS	Single Pulse Avalanche Energy ³	355	mJ
I_{AS}	Avalanche Current	-75	A
$P_D@T_C=25^\circ\text{C}$	Total Power Dissipation ⁴	270	W
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient ¹	---	50	$^\circ\text{C/W}$
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	---	0.4	$^\circ\text{C/W}$

P-Ch 100V Fast Switching MOSFETs
Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=-250\mu A$	-100	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=-10V$, $I_D=-20A$	---	8.5	10	m Ω
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=-250\mu A$	-2.0	-2.8	-4.0	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=-80V$, $V_{GS}=0V$, $T_J=25^\circ\text{C}$	---	---	-1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	2.1	---	Ω
Q_g	Total Gate Charge	$V_{DS}=-50V$, $V_{GS}=-10V$, $I_D=-20A$	---	78	---	nC
Q_{gs}	Gate-Source Charge		---	21	---	
Q_{gd}	Gate-Drain Charge		---	19.5	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=-50V$, $V_{GS}=-10V$, $R_G=3.3\Omega$, $I_D=-20A$	---	17	---	ns
T_r	Rise Time		---	42	---	
$T_{d(off)}$	Turn-Off Delay Time		---	46	---	
T_f	Fall Time		---	42	---	
C_{iss}	Input Capacitance	$V_{DS}=-50V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	6550	---	pF
C_{oss}	Output Capacitance		---	2123	---	
C_{rss}	Reverse Transfer Capacitance		---	145	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current ^{1,5}	$V_G=V_D=0V$, Force Current	---	---	-150	A
V_{SD}	Diode Forward Voltage ²	$V_{GS}=0V$, $I_S=-1A$, $T_J=25^\circ\text{C}$	---	---	1.2	V

Note :

- 1.The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$
- 3.The EAS data shows Max. rating . The test condition is $V_{DD}=-50V$, $V_{GS}=-10V$, $L=0.5mH$, $I_{AS}=-75A$
- 4.The power dissipation is limited by 150°C junction temperature
- 5.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.



Typical Characteristics

P-Ch 100V Fast Switching MOSFETs




Fig.1 Typical Output Characteristics




Fig.2 On-Resistance vs. G-S Voltage




Fig.3 Typical S-D Diode Forward Voltage




Fig.4 Gate-Charge Characteristics




Fig.5 Normalized $V_{GS(th)}$ vs. T_J




Fig.6 Normalized $R_{DS(on)}$ vs. T_J



P-Ch 100V Fast Switching MOSFETs




Fig.7 Capacitance




Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform





Fig.11 Unclamped Inductive Waveform

Ordering Information

Part Number	Package code	Packaging
HSY0149A	TOLL	2000/Tape&Reel

TOLL Package Outline



COMMON DIMENSIONS(MM)							
SYMBOL	MIN.	NOMINAL	MAX.	SYMBOL	MIN.	NOMINAL	MAX.
A	2.20	2.30	2.40	E1	8.20	8.30	8.40
b	0.70	0.80	0.90	E2	8.35	8.50	8.65
b1	9.70	9.80	9.90	H	11.50	11.68	11.85
b2	0.36	0.45	0.55	K	4.08	4.18	4.28
b3	0.05	0.100	0.35	K1	2.45	---	---
b4	0.30	0.40	0.50	L	1.60	1.90	2.10
b5	1.10	1.20	1.30	L1	0.50	0.70	0.90
b6	3.00	3.10	3.20	L2	0.50	0.60	0.70
C	0.40	0.50	0.60	L3	1.00	1.20	1.30
D	10.28	10.38	10.55	L4	0.13	0.23	0.33
D1	10.98	11.08	11.18	P	2.85	3.00	3.15
D2	3.20	3.30	3.40	θ	10°REF		
D3	7.00	7.15	7.30	aaa	0.20		
D4	3.44	3.59	3.74	ccC	0.20		
e	1.10	1.20	1.30	ddd	0.25		
E	9.80	9.90	10.00	eee	0.20		

HSY0149A Marking:

