



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

SPECIFICATIONS:

- 1.VOLTAGE/CURRENT RATING: 30V/0.3A AC;
- 2.WITHSTANDING VOLTAGE: 100V AC ONE MINUTE;
- 3.INSULATION RESISTANCE: 50M Ω MIN;
- 4.CONTACT RESISTANCE: 100m Ω MAX;
- 5.OPERATING TEMPERATURE RANGE: -35°C TO 85°C.

MATERIAL:

- 1.INSULATOR: LCP UL 94V-0 BLACK;
- 2.TERMINAL: COPPER ALLOY;
- 3.METAL FITTINGS: COPPER ALLOY.

PLATING:

- 1.TERMINAL: GOLD PLATING,
NICKEL 50u" MIN. OVER ALL;
- 2.METAL FITTINGS: TIN 100u" MIN. OVER NICKEL
50u"MIN.

Model	PIN	DIM A	DIM B	DIM C
JXT-0.4V08-10PDP	10	3.80	3.20	1.60
JXT-0.4V08-12PDP	12	4.20	3.60	2.00
JXT-0.4V08-16PDP	16	5.00	4.40	2.80
JXT-0.4V08-20PDP	20	5.80	5.20	3.60
JXT-0.4V08-24PDP	24	6.60	6.00	4.40
JXT-0.4V08-30PDP	30	7.80	7.20	5.60
JXT-0.4V08-34PDP	34	8.60	8.00	6.40
JXT-0.4V08-40PDP	40	9.80	9.20	7.60
JXT-0.4V08-50PDP	50	11.80	11.20	9.60

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.25	±1°	PART NO. JXT-0.4V08-NPDP	TITLE: BTB P0.40 HAEDER		
X.X±0.20			MANUFACTURE DWG		
X.XX±0.10					
UNITS	mm	DESIGN: Ethan			
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1

