





SCHEMATIC



P.C.B LAYOUT



MATAL	X
SUS	0.2mm
PBS	0.25mm

PIN	φ1.45	φ2.0	φ2.35	φ2.5
APPD.				

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		A1	2017.04.28	更新材质	GYW		
					UP TO 5mm: ±0.1	ANGULAR						
6	DC005 PING	BRASS	1	Ni PLATED	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS	BY	APPD	
5	DC005 4#FLAT PIECE 2.5	BRASS	1	Ag PLATED	TITLE : DC JACK			UNIT : MM	ROHS COMPLIANT	DWN		
4	DC005 2#CURVE PIECE 2.5	BRASS	1	Ag PLATED	MODEL : DC-005S-2.0-PU-R			SCALE: 4:1	CHK'D			
3	DC005 3#SPRING 2.5	PBS/SUS	1	Ag PLATED	HAOYU(HONGKONG)LIMITED			APPD				
2	DC005 COVER	PBT	1	BLACK/RED/YELLOW	皓宇(香港)有限公司			PRO.AGL:		REV :A1		
1	DC005 CASE	PBT	1	BLACK/RED/YELLOW								