


FEATURES

- Plastic SMD package
- Low leakage current: typ. 3 pA
- Switching time: typ. 0.8 μ s
- Continuous reverse voltage: max. 75 V



APPLICATION

- Low-leakage current applications in surface mounted circuits.

SOD-323

LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC 134).

| SYMBOL | PARAMETER | CONDITIONS | MIN. | MAX. | UNIT |
|------------------|-------------------------------------|---|------|------|------------------|
| Per diode | | | | | |
| V_{RRM} | repetitive peak reverse voltage | | — | 85 | V |
| V_R | continuous reverse voltage | | — | 75 | V |
| I_F | continuous forward current | single diode loaded; note 1; see Fig.2 | — | 160 | mA |
| | | double diode loaded; note 1; see Fig.2 | — | 140 | mA |
| I_{FRM} | repetitive peak forward current | | — | 500 | mA |
| I_{FSM} | non-repetitive peak forward current | square wave; $T_j = 25^\circ\text{C}$ prior to surge; see Fig.4 | — | 4 | A |
| | | $t_p = 1\ \mu\text{s}$ | | 1 | A |
| | | $t_p = 1\ \text{ms}$ | | 0.5 | A |
| | | $t_p = 1\ \text{s}$ | | | |
| P_{tot} | total power dissipation | $T_{amb} = 25^\circ\text{C}$; note 1 | — | 250 | mW |
| T_{stg} | storage temperature | | -65 | +150 | $^\circ\text{C}$ |
| T_j | junction temperature | | — | 150 | $^\circ\text{C}$ |


ELECTRICAL CHARACTERISTICS $T_j = 25^\circ\text{C}$ unless otherwise specified.

| SYMBOL | PARAMETER | CONDITIONS | TYP. | MAX. | UNIT |
|------------------|-----------------------|--|--------|------|---------------|
| Per diode | | | | | |
| V_F | forward voltage | see Fig.3 | — | 900 | mV |
| | | $I_F = 1\ \text{mA}$ | | | |
| | | $I_F = 10\ \text{mA}$ | | | |
| | | $I_F = 50\ \text{mA}$ | | | |
| | | $I_F = 150\ \text{mA}$ | | | |
| I_R | reverse current | see Fig.5 | 0.0033 | 5 | nA |
| | | $V_R = 75\ \text{V}$ $V_R = 75\ \text{V}; T_j = 150^\circ\text{C}$ | | 80 | A |
| C_d | diode capacitance | $f = 1\ \text{MHz}; V_R = 0$; see Fig.6 | 2 | — | pF |
| t_{rr} | reverse recovery time | when switched from $I_F = 10\ \text{mA}$ to $I_R = 10\ \text{mA}$; $R_L = 100\ \Omega$; measured at $I_R = 1\ \text{mA}$; see Fig.7 | 0.8 | 3 | μs |

Note


1. Device mounted on a FR4 printed-circuit board.

Typical Characteristics




Device mounted on a FR4 printed-circuit board.

Fig.2 Maximum permissible continuous forward current as a function of ambient temperature.



- (1) $T_J = 150\text{ }^{\circ}\text{C}$; typical values.
- (2) $T_J = 25\text{ }^{\circ}\text{C}$; typical values.
- (3) $T_J = 25\text{ }^{\circ}\text{C}$; maximum values.


Fig.3 Forward current as a function of forward voltage; per diode.



Based on square wave currents; $T_J = 25\text{ }^{\circ}\text{C}$ prior to surge.

Fig.4 Maximum permissible non-repetitive peak forward current as a function of pulse duration per diode.


Typical Characteristics



$V_R = 75$ V.

- (1) Maximum values.
(2) Typical values.

Fig.5 Reverse current as a function of junction temperature; per diode.




$f = 1$ MHz; $T_J = 25$ °C.

Fig.6 Diode capacitance as a function of reverse voltage; per diode; typical values.

PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SOD-323



Revision History

| Rev. | Change | Date |
|------|-----------------|-----------|
| V1.0 | Initial version | 2/23/2024 |
| | | |

Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsemsemi.com or visit www.jsemsemi.com