





SCHEMATIC



P.C.B LAYOUT



MATAL	X
SUS	0.2mm
PBS	0.25mm

PIN	Ø1.45	Ø2.0	Ø2.35	Ø2.5
APPD.				

					TOLERANCE UNLESS SPECIFIED							
6	DC005 PING	BRASS	1	Ni PLATED	UP TO 5mm: ±0.1	ANGULAR	A1	2017.04.28	更新材质		GYW	
5	DC005 4#FLAT PIECE 2.5	BRASS	1	Ag PLATED	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
4	DC005 2#CURVE PIECE 2.5	BRASS	1	Ag PLATED	TITLE : DC JACK			UNIT : MM	ROHS	DWN		
3	DC005 3#SPRING 2.5	PBS/SUS	1	Ag PLATED	MODEL : DC-005S-2.0-PU-G			SCALE: 4:1	COMPLIANT	CHK'D		
2	DC005 COVER	PBT	1	BLACK/RED/YELLOW	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司					APPD		
1	DC005 CASE	PBT	1	BLACK/RED/YELLOW						PRO.AGL:  		REV :A1
NO.	PART NAME	MATERIAL	QTY	FINISHING								