



| PIN   | $\phi 2.0$           | $\phi 2.5$           | $\phi 3.0$           |
|-------|----------------------|----------------------|----------------------|
| DIM A | $\phi 6.3 \pm 0.05$  | $\phi 6.3 \pm 0.05$  | $\phi 6.55 \pm 0.05$ |
| DIM B | $\phi 2.05 \pm 0.10$ | $\phi 2.55 \pm 0.10$ | $\phi 3.05 \pm 0.10$ |

| Model No.       | DC-062 | DC-062-1 |
|-----------------|--------|----------|
| Schematic       |        |          |
| CIRCUIT DIAGRAM |        |          |

SECTION A-A  
(插针规格:  $\phi 3.0$ )

SECTION A-A  
(插针规格:  $\phi 2.0$  &  $\phi 2.5$ )

|     |                         |          |     |              | TOLERANCE<br>UNLESS SPECIFIED        |               |    |      |            |                |
|-----|-------------------------|----------|-----|--------------|--------------------------------------|---------------|----|------|------------|----------------|
| 6   | Shunt Terminal [3]      | BRASS    | 1   | Ag/Sn-PLATED | UP TO 5mm: $\pm 0.1$                 | ANGULAR       | 1  |      |            |                |
| 5   | Tip spring [2]          | SUS      | 1   | Ag/Sn-PLATED | ABOVE 5mm: $\pm 0.2$                 | $\pm 1^\circ$ | NO | DATE | REVISIONS  | BY APPD        |
| 4   | Center pin terminal [1] | BRASS    | 1   | Ag/Sn-PLATED | TITLE: DC JACK                       |               |    |      | UNIT: MM   | ROHS COMPLIANT |
| 3   | Center pin              | BRASS    | 1   | Sn PLATED    | MODEL: DC-062-2.5                    |               |    |      | SCALE: 3:1 | CHK'D          |
| 2   | Cover                   | PBT      | 1   | BLACK        | HAOYU(HONGKONG)LIMITED<br>皓宇(香港)有限公司 |               |    |      | APPD       |                |
| 1   | Housing                 | PBT      | 1   | BLACK        |                                      |               |    |      |            |                |
| NO. | PART NAME               | MATERIAL | QTY | FINISHING    |                                      |               |    |      | PRO.AGL:   | REV :A0        |