








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

Specifications:
Electrical:

- 1.Current Rating
1.5A/contact terminal
- 2.Voltage Rating
30V DC
- 3.Contact Resistance
30 milliohms MAX
- 4.Dielectric Withstanding Voitage:
500 V AC AT Sea Level
- 5.Lnsulation Resistance:
1000MEGA ohms MIN

Mechanical:

- 1.Cnnector Mate and Unmate Force
Mate force:3.75kgf(MAX)
Unmate force:1.02kgf(MIN)
- 2.Terminal Retenion
1.2kgf(MIN)

Matorial:

- 1.Housing:
Hing Temperature
Tnermaplastics,
UI 94V-0 PBT White
 - 2.Contact:Copper Alloy C2680
 - 3.Shell: Copper Alloy C2680/SPCC
- Finish:
- 1.Contact: Plated Gold in Mating Area;
 - 2.Shell: Tin On Solder Talls.
Nickel Plating

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.30	X.*±3°	PART NO. Type-B-BF90	TITLE: USB B/F 90°DIP(弯脚)		
X.X±0.20	X.X*±2°				
X.XX±0.10			MANUFACTURE DWG		
UNITS	mm	DESIGN:	Ethan		SCALE N:A
MATERILA	---	CHED:	Olvia		
FINISH	---	APPD:	Ava		
					SHEET 1/1