







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insulator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PA6T
Max.Processing Temp: 240°C for30-60seconds
(260°Cfor10seconds)



P/N	PIN	DIM.A	DIM.B
IDC254-2-03Z	2*3	5.08	7.62
IDC254-2-04Z	2*4	7.62	10.16
IDC254-2-05Z	2*5	10.16	12.70
IDC254-2-06Z	2*6	12.70	15.24
IDC254-2-07Z	2*7	15.24	17.78
IDC254-2-08Z	2*8	17.78	20.32
IDC254-2-09Z	2*9	20.32	22.86
IDC254-2-10Z	2*10	22.86	25.40
IDC254-2-12Z	2*12	27.94	30.48
IDC254-2-13Z	2*13	30.48	33.02
IDC254-2-14Z	2*14	33.02	35.56
IDC254-2-15Z	2*15	35.56	38.10
IDC254-2-16Z	2*16	38.10	40.64
IDC254-2-17Z	2*17	40.64	43.18
IDC254-2-18Z	2*18	43.18	45.72
IDC254-2-20Z	2*20	48.26	50.80
IDC254-2-22Z	2*22	53.34	55.88
IDC254-2-25Z	2*25	60.96	63.50
IDC254-2-30Z	2*30	73.66	76.20
IDC254-2-32Z	2*32	78.74	81.28

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.±0.30	X.°±5°	PART NO. IDC254-2-NZ	TITLE: 2.54DC3-NPIn H8.9 180度 PC3.2 L11.5 6T			
X.X±0.20	X.X°±2°					
X.XX±0.10	X.XX°±1°					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG			
MATERILA	— — —	CHED: Olvia				
FINISH	— — —	APPD: Ava		SCALE	SHEET	
					N:A	1/1