







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insrlator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PA6T
Max.Processing Temp: 240°C for30-60seconds
(260°Cfor10seconds)



P/N	PIN	DIM.A	DIM.B
IDC2.54-2*3PW	2*3	5.08	7.62
IDC2.54-2*4PW	2*4	7.62	10.16
IDC2.54-2*5PW	2*5	10.16	12.70
IDC2.54-2*6PW	2*6	12.70	15.24
IDC2.54-2*7PW	2*7	15.24	17.78
IDC2.54-2*8PW	2*8	17.78	20.32
IDC2.54-2*9PW	2*9	20.32	22.86
IDC2.54-2*10PW	2*10	22.86	25.40
IDC2.54-2*12PW	2*12	27.94	30.48
IDC2.54-2*13PW	2*13	30.48	33.02
IDC2.54-2*14PW	2*14	33.02	35.56
IDC2.54-2*15PW	2*15	35.56	38.10
IDC2.54-2*16PW	2*16	38.10	40.64
IDC2.54-2*17PW	2*17	40.64	43.18
IDC2.54-2*18PW	2*18	43.18	45.72
IDC2.54-2*20PW	2*20	48.26	50.80
IDC2.54-2*22PW	2*22	53.34	55.88
IDC2.54-2*25PW	2*25	60.96	63.50
IDC2.54-2*30PW	2*30	73.66	76.20
IDC2.54-2*32PW	2*32	78.74	81.28

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.30	X.°±5°	PART NO. IDC2.54-2*NPW	TITLE: 2.0DC3-nPin H5.7 90° PC2.8 PB9.3 L10.5/14.5 6T		
X.X±0.20	X.X°±1°				
X.XX±0.10	X.XX°±0.5°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1