

LH15-23B 系列

----- 标准封装 AC-DC 模块电源 15W



产品特性

- 宽电压输入范围 85~305VAC (100~430VDC)
- 工作温度 -40℃~+70℃
- 保护功能齐全 (短路保护自恢复等)
- 高效率、高可靠性
- 稳压输出、低纹波噪声
- 工业级产品技术设计

应用范围

无线网络、电信/数据通信、电力系统、工业控制系统、测量仪器仪表、智能化领域等电源系统。适合于需要实现输入范围波动大，需要电源隔离，布板空间小等设计，并实现产品功能模块化，提高产品可靠性。

产品型号 Product Model

型号 Model	输出电压 Output Voltage (Vo)	输出电流 Io Output Current (Io)	效率 (TYP)
LH15-23B05R2	5V	3000mA	81%
LH15-23B12R2	12V	1250mA	84%
LH15-23B15R2	15V	1000mA	85%
LH15-23B24R2	24V	625mA	86%

*如有其它规格型号需求，可直接联系我司。For other specifications or models, please contact us directly.

输入特性 Input Characteristics

输入电压范围 Input Voltage Range	85~305VAC (100~430VDC)		
输入频率 Input Frequency	47~63Hz		
输入电流 Input Current	370mA (TYP) @115VAc	220mA (TYP) @ 230VAc	
外接保险丝 (推荐值) Recommended External Fuse	2A/250V 慢断		

输出特性 Output Characteristics

输出电压稳压精度 (主路) Output Voltage Regulation Accuracy (Main Channel)	±2%
源效应 (主路) Line Regulation (Main Channel)	±0.5% (typ)
负载调整率 Load Regulation (10%~100%)	±1% (typ)
最小负载 Minimum Load	10%

输出纹波+噪声 (峰-峰值) Output Ripple and Noise (Peak-to-Peak)	100mV(typ) (20MHz Bandwidth)
短路保护 Short-Circuit Protection	可长期短路, 自恢复 Sustained Short-Circuit, Auto-Recovery
输出过压保护 Output Over - Voltage Protection	≥1.1 倍

一般特性 General Characteristics

温度特性 Temperature Characteristics	工作温度 Op. Temp.	-40℃~+70℃
	功率降额 Power Derating	3.75% / °C ,
	存储温度 Storage Temperature	-40℃~+90℃
	外壳温度 Case Temp.	+90℃ max
掉电时间 Power-Off Delay		40ms(typ) / at Vin:320Vdc
湿度 Humidity		85%RH(max)
温漂 Temperature Drift		0.02%/°C
开关频率 Switching Frequency		65kHz(typ)
隔离电压 Isolation Voltage	输入--输出 Input-Output	3000Vac/1Min
	输出--输出 Output-Output	500Vdc/1Min
漏电流 Leakage Current		<5mA RMS typ. 230VAC/50Hz
*电磁兼容静电放电 EMC-ESD	IEC/EN 61000-4-2 level 3	6kV/8kV
*射频辐射抗扰 RFI	IEC/EN 61000-4-3	
*电快速瞬变脉冲群 EFT/B	IEC/EN 61000-4-4 level 3	2 kV
*浪涌 Surge	IEC/EN 61000-4-5 level 3	1kV/2kV
*传导/辐射 Conduction / Radiation		EN55022, level A
安全等级 Safety Class		CLASS I
外壳等级 Enclosure Class		阻燃塑料 UL94V-0
安装 Mounting Method		PCB
MTBF		>200,000h @25°C


注: 1. 标注*测试项目, 需增加外围 EMC 推荐电路;

For test items marked with an asterisk (*), the external EMC recommended circuit shall be added during testing.


2. 以上所列数据除特别说明外, 都是在 TA=25°C, 湿度<75%的条件下测得。

Unless otherwise specified, all data listed above are measured under the conditions of ambient temperature (T/A) = 25°C and relative humidity < 75%.

典型应用 Typical Applications





EMC 推荐电路




器件 Component	推荐值 Recommended Value
MOV	14D471
CY1、CY2	1000pF/400VAC
CX	0.1uF/275VAC
LCM	>10mH
L1	4.7uH/2A
FUSE	2A/250V, 慢断

输入电压与负载关系图
Input Voltage vs. Load Correlation

温度与负载关系图
Temperature vs. Load Correlation



外观和尺寸 Mechanical Specifications



Unit: mm Tolerance: $\pm 0.5\text{mm}$

尺寸说明 Dimensions Note:

Mark	A	B	C	D	E	F	G	H
Dimensions	17.5	62	54	5	20	45	22.5	4

引脚定义 Pin Definition:

Pin	1	2	3	4	5	6	7	8
Definition	AC(L)	AC(N)	NC	-Vo	NP	NP	NP	+Vo

珠海励至科技有限公司
E-mail: sales@lyztec.com
TEL: 0756-6358688
WEB: WWW. LYZTEC. COM