







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000MΩ, Min
Contact Resistance: 20mΩ, Max
Withstanding Voltage: AC 500V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
IDC2.0-2*3PZ	2*3	4.00	6.00
IDC2.0-2*4PZ	2*4	6.00	8.00
IDC2.0-2*5PZ	2*5	8.00	10.00
IDC2.0-2*6PZ	2*6	10.00	12.00
IDC2.0-2*7PZ	2*7	12.00	14.00
IDC2.0-2*8PZ	2*8	14.00	16.00
IDC2.0-2*9PZ	2*9	16.00	18.00
IDC2.0-2*10PZ	2*10	18.00	20.00
IDC2.0-2*11PZ	2*11	20.00	22.00
.....			
IDC2.0-2*35PZ	2*35	PIN-2.00	PIN

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.30	X.*±5°	PART NO. IDC2.0-2*NPZ	TITLE: 2.0DC3-nPin H5.7 180度 PC2.8 L8.0 6T		
X.X±0.20	X.X*±1°				
X.XX±0.10	X.XX*±0.5°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava		SCALE N:A	SHEET 1/1