







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insulator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PA6T
Max.Processing Temp: 240°C for30-60seconds
(260°Cfor10seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
254V-6P-B	2*3	5.08	7.62
254V-8P-B	2*4	7.62	10.16
254V-10P-B	2*5	10.16	12.70
254V-12P-B	2*6	12.70	15.24
254V-14P-B	2*7	15.24	17.78
254V-16P-B	2*8	17.78	20.32
254V-18P-B	2*9	20.32	22.86
254V-20P-B	2*10	22.86	25.40
254V-24P-B	2*12	27.94	30.48
254V-26P-B	2*13	30.48	33.02
254V-28P-B	2*14	33.02	35.56
254V-30P-B	2*15	35.56	38.10
254V-32P-B	2*16	38.10	40.64
254V-34P-B	2*17	40.64	43.18
254V-36P-B	2*18	43.18	45.72
254V-40P-B	2*20	48.26	50.80
254V-44P-B	2*22	53.34	55.88
254V-50P-B	2*25	60.96	63.50
254V-60P-B	2*30	73.66	76.20
254V-62P-B	2*32	78.74	81.28

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.30	X.*±5°	PART NO. 254V-NP-B	TITLE: 2.54DC3-NPIn H8.9 180度 PC3.2 L11.5 6T		
X.X±0.20	X.X*±2°				
X.XX±0.10	X.XX*±1°				
UNITS	mm	DESIGN:	Ethan	MANUFACTURE DWG	
MATERILA	---	CHED:	Olvia		
FINISH	---	APPD:	Ava		SCALE N:A
					SHEET 1/1