


Features & Applications

Super high density cell design for extremely low $R_{DS(ON)}$.
 Exceptional on-resistance and maximum DC current capability.
 ESD Protection.



Absolute Maximum Ratings($T_a=25^{\circ}\text{C}$)

Symbol	Parameter	Value	Unit
V_{DS}	Drain-Source Voltage	-50	V
V_{GS}	Gate-Source Voltage	± 20	V
I_D	Continuous Drain Current	-0.13	A
I_{DM}	Pulsed Drain Current ($t_p=10\text{s}$)	-0.5	A
P_D	Power Dissipation	350	mW
$R_{\theta JA}$	Thermal Resistance From Junction To Ambient ($t \leq 5\text{s}$)	350	$^{\circ}\text{C/W}$
T_J, T_{stg}	Operation Junction And Storage Temperature Range	$-55 \sim +150$	$^{\circ}\text{C}$

Electrical Characteristics ($T_a=25^{\circ}\text{C}$ unless otherwise specified)

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
Static						
V _{(BR)DSS}	Drain-source breakdown voltage	V _{GS} =0, I _D =250μA	-50			V
V _{GS(th)}	Gate threshold voltage	V _{DS} =V _{GS} , I _D =-250μA	-0.8		-2.0	V
I _{GSS}	Gate-body leakage current	V _{DS} =0, V _{GS} =±10V			±10	μA
I _{DSS}	Zero gate voltage drain current	V _{DS} =-50V, V _{GS} =0V			-10	μA
		V _{DS} =-40V, V _{GS} =0V			-100	nA
R _{DS(on)}	Drain-source on-resistance ^a	V _{GS} =-10V, I _D =-0.13A		2	5	Ω
		V _{GS} =-4.5V, I _D =-0.13A		2.5	6	Ω
g _{FS}	Forward transconductance ^a	V _{DS} =-25V, I _D =-0.13A	50			mS
V _{SD}	Diode forward voltage	I _S =-0.13A, V _{GS} =0V			-1.0	V
Dynamic						
C _{iss}	Input capacitance	V _{DS} =-25V, V _{GS} =0V, f=1MHz		25		pF
C _{oss}	Output capacitance			15		
C _{rss}	Reverse transfer capacitance ^b			3.5		
Switching ^b						
t _{d(on)}	Turn-on delay time	V _{GS} =-10V, V _{DS} =-15V I _D =-200mA, R _{GEN} =25Ω		16.7		nS
t _r	Rise time			8.6		
t _{d(off)}	Turn-off delay time			17.9		
t _f	Fall time			5.3		

Notes :

a. Pulse Test : Pulse width $\leq 300\mu\text{s}$, duty cycle $\leq 2\%$.

b. Guaranteed by design, not subject to producing.

Typical Characteristics




Figure1. Output Characteristics




Figure2. Transfer Characteristics




Figure3. Drain-Source on Resistance




Figure4. Drain-Source on Resistance




Figure5. Diode Forward Voltage vs. current





Figure6. Gate Threshold vs. Junction Temperature

Package Information

SOT-23



Symbol	Dimensions in Millimeters(mm)		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950TYP		0.037TYP	
e1	1.800	2.000	0.071	0.079
L	0.550REF		0.022REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°

Revision History

Rev.	Change	Date
V1.0	Initial version	2/23/2024

Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsmsemi.com or visit www.jsmsemi.com