

A

B

C

D

E






A

B

C

D

E



GT-FH2541 D V 50 - 2 XX X XX X 01

G-Switch

Series No

Termipoint

D-DIP

ANGLE

V-180°

Height

50-5.0mm

Material
B-PBT
C-PA6T
E-PA9T
D-LCP
F-PA66

Terminal Plating
11- All G/F

Housing Colour
B-Black

Pin Q' PY
04-80

Row number
2-Double Rows

G-Switch Specification:

- 1.Current rated: 3.0A AC/DC
- 2.Voltage rating: 500V AC/DC
- 3.Withstanding voltage: 1000V AC for 1 min
- 4.Contact resistance: 20mΩ max.
- 5.Insulation resistance: 1000MΩ min
- 6.Durability cycle: 100Cycles
- 7.Removal force: 0.60kgf/Pin min
- 8.Operating temperature range: -40°C ~ +105°C

2	PIN MATERIAL	BARSS	ALL G/F
1	HOUSING	PA6T,94V-0	BLACK
NO.	PART NAME	MATERIAL	REMARK



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X ± 0.40
X.x ± 0.30
X.xx ± 0.20
X° $\pm 5^\circ$
X.x° $\pm 3^\circ$

Title: FH 2.54mm Pitch Pin Header Dual Dow
DIP Type 2xNP PC3.00mm

Molde Code: GT-FH2541DV50-2XXXXXX01

DRAWN	CHECKED	APPROVED	DATE
Hu	Hu	Chen	2022.12.20

品赞科技
b-Switch
www.dg-switch.com

REV: A0 SHEET: 1/1