



LOC		DIST		REVISIONS					
—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
					G2	TOLERANCE CORRECTION	23JUL2013	KJK	RP

NOTES:

- 1 FOR MINI-APPLICATOR CRIMPING.
- 2 UNDERCOATING:1,25µm Ni,SELECTIVE:0,8µm Au, ZONE 1: 0,5µm MIN. GOLD FLASH.
- 3 UNDERCOATING:1,25µm Ni,SELECTIVE:0,8µm Au, REMAINDER: GOLD FLASH.
- 4 ZONE 1:BRIGHT TIN/LEAD PLATED.
- 5 PRE-TIN PLATED 2,0µm.
- 6 MATERIAL: PHOSPHOR BRONZE
- 7 OBSOLETE



WIRE RANGE :
0,20-0,58 mm² 24-20 AWG
INSULATION RANGE :
1,6 MAX. DIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.v.LIEMPT 03 DEC 98	 TE Connectivity			
		CHK J.v.LIEMPT				
		APVD E.LEIJTENS	NAME			
		PRODUCT SPEC	AMPMODU MOD.4 RECEPTACLE, S.C.P. STRIP			
		APPLICATION SPEC				
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-167418	RESTRICTED TO
CUSTOMER DRAWING		SCALE 8:1		SHEET 1 OF 1		REV G2