

GRAIN DIRECTION

NOTE:

1. ALL INSIDE BEND RADII TO BE A MIN. OF MATERIAL THICKNESS UNLESS OTHERWISE SPECIFIED.
2. PART MUST BE FREE OF ALL BURRS AND SHARP EDGES.
3. MAT' L: 0.254 TH' K FULL HARD PHOSPHOR BRONZE
4. FINISH: NICKEL PLATE
0.00254-0.00762 NICKEL, OVER
0.00127-0.00254 COPPER
5. INDICATES CRITICAL DIMENSION

NOTES:

1. MATERIAL :
0.30mm PHOSPHOR BRONZE, NICKEL PLTD.
2. ROHS 2 COMPLIANT
Order code:

BS - M - SI - R - CR3002A
① ② ③ ④ ⑤

- ① BS: Battery Contacts
- ② Apperance for the product
M:SMT TYPE
- ③ Contact PIating
SI:Nickel Plate
SN:Tin
G0:Gold flash
G1: 3U" Gold
G2: 5U" Gold
G3:10U" Gold
G4:15U" Gold
G5:30U" Gold
- ④ Packing:
B: Bag bulk packing
R: Tape & Reel packing
- ⑤ Product number
CR3002A


Unless Otherwise specified tolerance	
X. ± 0.35	X.XX: ± 0.20
X.X: ± 0.25	X.XXX: ± 0.15
SCALE: As Shown	UNIT: mm
DRAW Lv Xun Hua	DATE 16/03/2019
CHECK BobYang	DATE 16/03/2019



TITLE: BATTERY CONTACTS FOR CR3002.BR2016.DL2020.
CR2025.CR2032

DRAWING NO: BS-M-SI-R-CR3002A

PRODUCT NO: BS-M-SI-R-CR3002A





	change BT-M-SN-3002-R to BS-M-SN-R-CR3002A	16/03/2019
REV	DESCRIPTION	DATE

HSF



RoHS



前后各空18个

- NOTES:
- TAPE AND REEL SPECIFICATIONS:
1. TAPE:
- MAT'L-ALL CONDUCTIVE POLYSTYRENE CARRIER
- ANSI/EIA-481 STANDARD
- 44.0 WIDE;24.0 PITCH
2. REEL:
- 330.2 DIA.500 PIECES OF
- PART NO.BS-M-SI-3002-R PER REEL.

Unless Otherwise specified tolerance

X. ±0.35 X.XX: ±0.20

X.X: ±0.25 X.XXX: ±0.15



SCALE:

As Shown

UNIT:

mm

DRAW

Lv Xun Hua

DATE

03/16/2019

CHECK

BobYang


DATE

03/16/2019

TITLE: BATTERY CONTACTS FOR CR3002. BR2016. DL2020. CR2025. CR2032

DRAWING NO: BS-M-SI-R-CR3002A

PRODUCT NO: BS-M-SI-R-CR3002A



3rd ANGLE PROJECTION

change BT-M-SN-3002-R to BS-M-SN-R-CR3002A

16/03/2019

REV

DESCRIPTION

DATE