





D



C



- 1 MATERIAL: HOUSING - UL 94V-0 RATED HIGH TEMP. NYLON, COLOR BLACK.
CONTACT - BRASS.
HOLDDOWNS - PHOSPHOR BRONZE.
- 2 MAXIMUM INSERTION 30 LBS.
- 3 RECOMMENDED BOARD THICKNESS 1.57.
- 4 FINISH: CONTACT - 0.76µm MINIMUM GOLD,
OR
0.0762µm MINIMUM GOLD FLASH OVER 0.69µm MINIMUM PALLADIUM NICKEL,
ON MATING AREA PER TE CONNECTIVITY'S DISCRETION,

2.54µm MINIMUM MATTE TIN ON SOLDER TAILS.

ALL OVER 1.27µm NICKEL MINIMUM.

HOLDDOWNS - 2.54µm MATTE TIN OVER 1.27µm NICKEL MINIMUM.
- 5 CUTTING AREA REGION, NO PLATING IS PRESENT.
- 6 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION).
- 7 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

B

	40.00	33.00	37.30	36.86	24	5-794682-4
OBSOLETE	-37.00	-30.00	-34.30	-33.86	-22	-5-794682-2-
OBSOLETE	-34.00	-27.00	-31.30	-30.86	-20	-5-794682-0-
OBSOLETE	-31.00	-24.00	-28.30	-27.86	-18	-4-794682-8-
OBSOLETE	-28.00	-21.00	-25.30	-24.86	-16	-4-794682-6-
	25.00	18.00	22.30	21.86	14	4-794682-4
	22.00	15.00	19.30	18.86	12	4-794682-2
	19.00	12.00	16.30	15.86	10	4-794682-0
	16.00	9.00	13.30	12.86	8	3-794682-8
	13.00	6.00	10.30	9.86	6	3-794682-6
	10.00	3.00	7.30	6.86	4	3-794682-4
	7.00	-	4.30	3.86	2	3-794682-2
	DIM A	DIM Z	DIM Y	DIM X	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±0.20
3 PLC	±
4 PLC	±
ANGLES	±1°
FINISH	

MATERIAL

1

DWN
B. HAYMAKER
CHK
K. COBLE
APVD
K. COBLE

16AUG99
16AUG99
16AUG99

PRODUCT SPEC
108-1836
APPLICATION SPEC
114-13000
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
VERTICAL HEADER ASSEMBLY,
THRU HOLE, 0.76Au or 0.69PdNi
DUAL ROW, MICRO MATE-N-LOK™

SIZE A2	CAGE CODE 00779	DRAWING NO C-794682	RESTRICTED TO -
SCALE 4:1			SHEET 1 OF 2
			REV G1

A

D

C

794682

B

A

