

Features

- Single supply range operating from 3.0V to 4.5V
- -118dB THD+N into 100kΩ load at 2Vrms
- -114dB THD+N into 32Ω load at 2Vrms
- Signal-to-Noise (SNR) Ratio 132dBA
- 100dB PSRR at 10kHz
- 145dB crosstalk & separation
- Pop/Click shunt circuit
- Audio Path Soft Turn-On/Off for Pop & Click Elimination
- operates over an ambient temperature range of -40°C to +85°C
- Packaging: WLCSP 1.2 x 1.2 -9 Ball

Applications


- Mobile Phones/Tablet PCs
- Notebook/Ultrabook Computers

PIN DESCRIPTION

General Description


The is an audio headset analog switch that is used to detect 3.5mm accessories and switch sleeve and ring by external controller. The ground signal is routed through a pair of low-impedance ground FETs (75mΩ typical), resulting minimal impact on audio cross-talk performance. The ground FETs of the device are designed to allow FM signal pass-through, making it possible to use the ground line of the headset as an FM antenna in mobile audio application.

PIN CONFIGURATIONS (TOP VIEW)



PIN	NAME	FUNCTION
A1	VDD	Power Supply for the Chip.
A2	GNDB	FET2 Ground Reference.
A3	RING2	Connected to the RING2 Segment of the Jack. This pin will be routed to MICP or GNDB depending on the logic level of SELECT pin.
B1	MICP	Microphone Signal Connection to Codec. Microphone bias should be fed into this pin.
B2	GNDA	FET1 Ground Reference.
B3	SLEEVE	Connected to the SLEEVE Segment of the Jack. This pin will be routed to MICP or GNDA depending on the logic level of SELECT pin.
C1	SELECT	The Logic Signal Used to Control S1 Switch, FET1 and FET2.
C2	NC	No Connection.
C3	GND	Chip Ground Reference.


Functional Diagram



Truth Table

SELECT	FUNCTION
0	MICP = A = SLEEVE, FET2 Turn On, FET1 Turn Off.
1	MICP = B = RING2, FET2 Turn Off, FET1 Turn On.

Typical Application



Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Supply Voltage	V_{CC}	-0.3 ~ 6	V
Voltage Range on SELECT, MICP, RING2, SLEEVE	V_{IS}	-0.3 ~ VDD+0.3V	V
Storage Temperature Range	T_{STG}	-55 ~ 150	°C
Junction Temperature	T_J	150	°C
Lead Temperature (Soldering, 10 seconds)	T_L	260	°C
Thermal Resistance	$R_{\theta JA}$	80	°C/W

Note:

Absolute Maximum Ratings” may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions beyond those indicated in the operational sections of this specification is not implied

Recommend operating ratings

Parameter	Symbol	Value	Unit
Supply Voltage	V_{CC}	2.6 ~ 5.0	V
Input/Output Voltage Range	V_{IN}	0.0 ~ 3.3	V
operates over an ambient temperature range	T_A	-40°C to +85	°C

Note:

The input and output negative voltage ratings may be exceeded if the input and output diode current ratings are observed.

DC Electrical Characteristics

($V_{DD} = 2.6V$ to $5.0V$, typical values are at $V_{DD} = 3.3V$, $T_A = +25^\circ C$, unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Input Voltage Range	VDD		2.6	--	5.0	V
Quiescent Current	IQ	VDD = 4.5V, VMICP = 1.8V to VDD, SELECT = Low or SELECT = High (after detection)	--	4	--	μA
Input/Output Voltage Range	VIO		0	--	3.3	V
Input Logic High for SELECT	VIH	VDD = 2.6V	1.1	--	VDD	V
		VDD = 3.3V	1.1	--	VDD	
		VDD = 4.5V	1.3	--	VDD	
Input Logic Low for SELECT	VIL	VDD = 2.6V	0	--	0.7	V
		VDD = 3.3V	0	--	0.8	
		VDD = 4.5V	0	--	0.8	
Pull Down Resistor of Select Pin	RPD		--	560	--	k Ω
FET1 On Resistance	RF1	VDD = 2.6V, VGND = 0V, IGND = 10mA	--	75	--	m Ω
FET2 On Resistance	RF2		--	75	--	
S1 On Resistance (Closed to A)	RS1A	VDD = 2.6V,	--	5	--	Ω
S1 On Resistance (Closed to B)	RS1B	VSLEEVE/RING2 = 0V to 2.6V, IMIC = $\pm 10mA$	--	5	-	


Note:

(1) Flatness is defined as the difference between maximum and minimum value of ON-resistance at the specified analog signal voltage points.

(2) R_{ON} matching between channels is calculated by subtracting the channel with the lowest max Ron value from the channel with the highest max Ron value.

Package information

WLCSP-9B(1.2X1.2) (Unit: mm)



Symbol	Dimensions In Millimeter		
	Min.	Typ.	Max.
X	1.145	1.17	1.195
Y	1.145	1.17	1.195
X1	--	0.185	--
X2	--	0.400	--
X3	0.245	0.270	0.295
Y1	--	0.185	--
Y2	--	0.400	--
Z	0.535	0.575	0.615
Z1	0.170	0.195	0.22
Z2	0.345	0.355	0.365
Z3	0.02	0.025	0.03