

HSF



RoHS

NOTES:

1. MATERIAL: ANNEALED SPRING STEEL, T=0.25mm.

2. PLATING:

80U" Min TIN PLATED OVERALL

50U" Min NICKEL PLATED UNDER OVERALL

Order code:

$$\frac{BS}{①} - \frac{M}{②} - \frac{SN}{③} - \frac{X}{④} - \frac{5230}{⑤}$$

① BS: Battery Contacts

② Apperance for the product

M:SMT TYPE

③ Contact Plating

SI:NICKEL PLATE

SN:Tin

G0: Gold flash

G1: 3u" Gold

G2: 5u" Gold

G3: 10u" Gold

G4: 15u" Gold

G5: 30u" Gold

④ Packing method


A: Tray packing

R: Tape & reel packing

B: Bag packing

⑤ Product number

5230: 5230 STYLE



Overall flatness of bottom
surface of shell.

All bending and forming
shall be adjustable.

Unless Otherwise specified tolerance
X. ± 0.30 X.XX: ± 0.15
X.X: ± 0.20 X.XXX: ± 0.05

SCALE: As Shown UNIT: mm

DRAW Tang Ming Xin DATE 9/18/2021

CHECK BobYang DATE 9/18/2021

3rd ANGLE PROJECTION

Antenk®

TITLE: Cell Battery Contacts 5230

DRAWING NO: BS - M - SI - X - 5230

PRODUCT NO: BS - M - SI - X - 5230

REV

DESCRIPTION

DATE