







RECOMMENDED PCB LAYOUT

PATTERN PROHIBITION AREA


NOTES:

1. MATERIAL:
 - 1-1. Insulator: High Temperature Thermoplastic, UL94V-0; Color Black.
 - 1-2. Terminal: Copper Alloy.
 - 1-3. Shell: Stainless Steel.
2. PLATING:
 - 2-1. Contact: Plated 50u" Ni Overall Contact Au 1u",
 - 2-2. Shell: Plated 50u" Ni Overall, PAD Au 1u"
3. SPECIALITY:
 - 3-1. Current Rating :0.5mA AC/DC max.
 - 3-2. Voltage Rating :125V AC/DC
 - 3-3. Ambient Temperature Range : -20°C~+60°C
 - 3-4. Storage Temperature Range : -40°C~+70°C
 - 3-5. Ambient Humidity Range :95% R.H. Max.
 - 3-6. Contact Resistance:100mΩ max.
 - 3-7. Insulation Resistance:1000MΩ min./500VDC
 - 3-8. Mating Cycles:10,000 Insertions
 - 3-9. Reflow peak temp.:260°C ±5°C, 3~5 S
 - 3-10. Mating Cycles:3,000 Insertions Min



SIM pin assignment	
PIN#	Name
C1	VCC供电电压
C2	RST重置
C3	CLK时钟
C5	GND接地
C6	VPP程序电压
C7	I/O输入输出


DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: NANO-SIM 6Pin 1.35H 板贴	
.X±0.3	X.*±3	CHK.	Jack	DWG NO. NANO SIM 6Pin 1.35h	
.XX±0.2	.X.*±2	DRA	Can	CUSTOMER DRAWING	
.XXX±0.1	.XX.*±	PROJ.		SIZE A4	SCALE 1:1
				SHEET 1/1	REV. A



NOTES

1. NUMBER OF CONNECTORS:1800PCS/REEL

2. LEAD TAPE LENGTH




3. QUANTITY:18000PCS/CARTON

4. WEIGHT :

3.1 NET WEIGHT : Kg

3.2 GROSS WEIGHT : Kg



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.3	X.*±3	APR.	Alex	TITLE: NANO-SIM 6Pin 1.35H 板	
.XX±0.2	.X.*±2	CHK.	Jack	DWG NO. NANO SIM 6Pin 1.35h	
.XXX±0.1	.XX.*±	DRA.	Can	PROJ.	CUSTOMER DRAWING
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		