







PRELIMINARY
DESIGN IS SUBJECT
TO CHANGE WITHOUT
PRIOR NOTICE

SECTION A-A

SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

技术要求:

- 1、塑件材料:PA66 (UL-94V-0)
- 2、接触件:黄铜镀锡
- 3、接触电阻: $\leq 10m\Omega$
- 4、绝缘电阻: $\geq 1000M\Omega$
- 5、额定电压:250V AC DC
- 6、额定电流:2.0A AC DC
- 7、耐压:能承受1000V AC/Minute
- 8、工作温度: $-25^{\circ}\sim +85^{\circ}$
- 9、可焊性试验:浸锡面积 $\geq 95\%$ 温度 $220\pm 5^{\circ}$, 时间 2.5 ± 0.5 秒
- 10、铅和镉等六大有害物质含量要符合环保要求

Part No	PIN	A	B
XY-PH2.0-2PWZ	2	2	6
XY-PH2.0-3PWZ	3	4	8
XY-PH2.0-4PWZ	4	6	10
XY-PH2.0-5PWZ	5	8	12
XY-PH2.0-6PWZ	6	10	14
XY-PH2.0-7PWZ	7	12	16
XY-PH2.0-8PWZ	8	14	18
XY-PH2.0-9PWZ	9	16	20
XY-PH2.0-10PWZ	10	18	22
XY-PH2.0-11PWZ	11	20	24
XY-PH2.0-12PWZ	12	22	26
XY-PH2.0-13PWZ	13	24	28
...	...	...	...
XY-PH2.0-20PWZ	20	(20-1)*2	(20+1)*2

2	Contact	Brass	n*1	电镀(锡): 整个表面镀底镍30u"MIN,再镀锡80u".MIN.
1	Wafer	PA66(UL94V-0)	1	本色
序号	名称	材料	数量	附注
DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
.X±0.35	X.*± 5°	APR. Alex	TITLE: WAFER 2.0mm H6.0mm 90° DIP	
.XX±0.25	.X.*± 3°	CHK. Jack	DWG NO. XY-PH2.0-NPWZ	
.XXX±0.15	.XX.*± 1°	DRA. Can	PROJ. 	CUSTOMER DRAWING
			SIZE A4	SCALE 1:1