








Part No	Pin	A	B	C
XY-FPC-05-09-4RLTAG	4	1.50	2.52	5.54
XY-FPC-05-09-5RLTAG	5	2.00	3.02	6.04
XY-FPC-05-09-6RLTAG	6	2.50	3.52	6.54
XY-FPC-05-09-7RLTAG	7	3.00	4.02	7.04
XY-FPC-05-09-8RLTAG	8	3.50	4.52	7.54
XY-FPC-05-09-9RLTAG	9	4.00	5.02	8.04
XY-FPC-05-09-10RLTAG	10	4.50	5.52	8.54
XY-FPC-05-09-11RLTAG	11	5.00	6.02	9.04
XY-FPC-05-09-12RLTAG	12	5.50	6.52	9.54
—	—	—	—	—
XY-FPC-05-09-60RLTAG	60	(60-1)*0.5	(60+1)*0.5+0.02	(60+7)*0.5+0.04
XY-FPC-05-09-80RLTAG	80	(80-1)*0.5	(80+1)*0.5+0.02	(80+7)*0.5+0.04



SECTION A-A



适用线路板(PCB LAYOUT)



序号	品名	材质
1	0.5mm铜箔(H2.0)	LCP UL94V-0 本色
2	0.5mm铜箔(H2.0)	铜合金/表面镀金
3	0.5mm铜箔(H2.0)	LCP UL94V-0 黑色
4	0.5mm铜箔(H2.0)	铜合金/表面镀金

适用扁平线(Applicable Flat Cable)

技术指标:

1. 塑件表面应光洁, 无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500M\Omega$ 。

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.3	X.*± 5°	APR.	Alex	TITLE: 0.5 Pitch H2.0 Backflip R/A Type CONN		
.XX±0.2	.X*± 2	CHK.	Jack	DWG NO. XY-FPC-05-09-NRLTAG		
.XXX±0.05	.XX*± 1°	DRA.	Can	PROJ. 		CUSTOMER DRAWING
				SIZE A4	SCALE 1:1	SHEET 1 / 1



NOTE:

1. MATERIAL:

HOUSING: LCP (UL94V-0), COLOR: NATURAL.

CONTACTS: COPPER ALLOY.

PEG: COPPER ALLOY.

ACTUATOR: LCP (UL94-V0), COLOR:BLACK

2. RATING:

OPERATING VOLTAGE: 50Vrms AC.

CURRENT RATING: 0.5A.

OPERATING TEMPERATURE: -55°C~+85°C.

OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

STORAGE TEMPERATURE RANGE: -10°C~+50°C.

STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

带 ⊙ 为重要管控尺寸

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 0.5Pitch 1.0H ZIF/翻盖式	
.X±0.35	.X*± 5°	CHK.	Jack	DWG NO. XY-FPC-05-09-NRLTAG	
.XX±0.2	.X*± 2	DRA.	Can	CUSTOMER DRAWING	
.XXX±0.05	.XX*± 1°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A