

SPECIFICATIONS

Current Rating: 1.0 Amps

Withstanding Voltage: AC 500V

Insulation Resistance: 1000MΩ Min

Contact Resistance: 20mΩ Max

Operation Temperature: -40°C to +105°C

Insulator Material: Polyester (UL94V-0)

Contact Material: Phosphor bronze



Standard: PA6T

Contact Plating: Gold Flash

Max. Processing Temp: 240°C for 30-60 seconds

(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
XY-PM127-2-01P-S-4.3	2*1	0.00	1.27
XY-PM127-2-02P-S-4.3	2*2	1.27	2.54
XY-PM127-2-03P-S-4.3	2*3	2.54	3.81
XY-PM127-2-04P-S-4.3	2*4	3.81	5.08
XY-PM127-2-05P-S-4.3	2*5	5.08	6.35
XY-PM127-2-06P-S-4.3	2*6	6.35	7.62
XY-PM127-2-07P-S-4.3	2*7	7.62	8.89
XY-PM127-2-08P-S-4.3	2*8	8.89	10.16
XY-PM127-2-09P-S-4.3	2*9	10.16	11.43
.....			
XY-PM127-2-50P-S-4.3	2*50	(PIN-1)x1.27	(PIN)x1.27



RECOMMEND P.C.B LAYOUT

PCB TOLERANCE: ±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司			
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyconn Electronics Co.,Ltd			
.X±0.3	.X°± 5°	APR.	Alex	TITLE: 1.27FH H4.3 2xNPin SMT U ₁ PC4.8 PB4.6 6T	
.XX±0.2	.X°± 1	CHK.	Jack	DWG NO. XY-PM127-2-NP-S-4.3	
.XXX±0.1	.XX°± 0.5	DRA.	Can	PROJ. 	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1