



TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	浙江创都电子科技有限公司			
X.X ±0.30	X.* ±10'	PART NO.	TITLE: TYPE-C-16P-BS-QCHT-3MD-7.35			
.XX ±0.20	.X* ± 8'	DESIGN: DRAW	DRAWG NO. DRAW_NO.			
.XXX ±0.10	.XX* ± 5'					
UNITS	mm					
MATERILA		CHED:				
FINISH		APPD:		SCALE	SHEET	REV.
				SCALE	SHEET	REV.

7. DATE CODE: AA AA
 WEEK
 YEAR



SECTION:A-A

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
C	ECN NO.	MODIFY NOTE	2020.06.23	SYJ
D	ECN NO.	UPDATE THE DRAWING	2020.08.03	SYJ



AFTER MATING


USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND

ORDER INFORMATION

P/N: ACF016-1XXH1A1XX-XHR


HOUSING MATERIAL	D/C
A: LCP	0: WITHOUT D/C
E: PA9T	1: WITH D/C
HOUSING COLOR	CONTACT FUNCTIONAL AREA PLATED
1: BLACK	01: Au 1u"
5: NATURE	03: Au 3u"
SHELL MATERIAL	15: Au 15u"
H:SUS304	30: Au 30u"
N: SK7	CONTACT SOLDER AREA PLATED
SHELL PLATING	1: Au 1u"
1: Ni	CONTACT METRIAL
	A: C1814






RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 0.80MM:DEFAULT TOLERANCE:±0.05

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	
X.X	±0.30	X.X	±10'
.XX	±0.20	.X	± 8'
.XXX	±0.10	.XX	± 5'
UNITS	mm	DESIGN: DRAW	DRAWG NO.
MATERILA		CHED:	DRAW_NO.
FINISH		APPD:	SCALE SHEET REV.
			SCALE SHEET REV.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
C	ECN NO.	MODIFY NOTE	2020.06.23	SYJ
D	ECN NO.	UPDATE THE DRAWING	2020.08.03	SYJ



SEE DETAIL X



DETAIL X

PAPER BOARD

REEL AND TAPE

REEL AND TAPE

PAPER BOARD

FOLDER
PAPER BOARD

CARTON

		REEL	CARTON
CONNECTOR (PCS)		1000	15000
NAME(INTENDED USE) CUSTOMER DRAWING			
PART NO.		TITLE:	
DESIGN: DRAW		DRAWG NO.	
MATERILA		CHED:	
FINISH		APPD:	
		SCALE	SHEET
		SCALE	SHEET
		REV.	REV.

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	
X.X	±0.30	X.'	±10'
.XX	±0.20	.X'	± 8'
.XXX	±0.10	.XX'	± 5'
UNITS	mm		
MATERILA		CHED:	
FINISH		APPD:	