






1	2	3	4	5	6	7	8	9	10																																																			
							REV.	ECN NO.	DESCRIPTION	APP.	DATE																																																	
							A																																																					
F											F																																																	
E	 6.65 2.05 PLUG AFTER MATING USB TYPE-C PIN ASSIGNMENTS <table><thead><tr><th>PIN NUMBER</th><th>SIGNAL NAME</th><th>PIN NUMBER</th><th>SIGNAL NAME</th></tr></thead><tbody><tr><td>A1</td><td>GND</td><td>B12</td><td>GND</td></tr><tr><td>A4</td><td>VBUS</td><td>B9</td><td>VBUS</td></tr><tr><td>A5</td><td>CC1</td><td>B8</td><td>SBU2</td></tr><tr><td>A6</td><td>Dp1</td><td>B7</td><td>Dn2</td></tr><tr><td>A7</td><td>Dn1</td><td>B6</td><td>Dp2</td></tr><tr><td>A8</td><td>SBU1</td><td>B5</td><td>CC2</td></tr><tr><td>A9</td><td>VBUS</td><td>B4</td><td>VBUS</td></tr><tr><td>A12</td><td>GND</td><td>B1</td><td>GND</td></tr></tbody></table>  6.40 4.80 3.50 2.50 1.50 0.50 0.30(12X) 0.60(4X) 1.80(2X) 0.80(2X) 4.00 4.60 5.70 2.10 9.24 11.24 0.60(4X) P.C.B EDGE PRODUCT EDGE										PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME	A1	GND	B12	GND	A4	VBUS	B9	VBUS	A5	CC1	B8	SBU2	A6	Dp1	B7	Dn2	A7	Dn1	B6	Dp2	A8	SBU1	B5	CC2	A9	VBUS	B4	VBUS	A12	GND	B1	GND	E													
PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME																																																									
A1	GND	B12	GND																																																									
A4	VBUS	B9	VBUS																																																									
A5	CC1	B8	SBU2																																																									
A6	Dp1	B7	Dn2																																																									
A7	Dn1	B6	Dp2																																																									
A8	SBU1	B5	CC2																																																									
A9	VBUS	B4	VBUS																																																									
A12	GND	B1	GND																																																									
D											D																																																	
C											C																																																	
B											B																																																	
A											A																																																	
THIS PRODUCT SHOULD MEET HAZARDOUS MATERIAL CONTROL DIERCTIVE OF JUN SHENG JIE FROM RAW MATERIAL TO MANUFACTURING, PACKAGE AND DELIVERY.							<table><tr><td>TOLERANCES 一般公差</td><td>UNIT : mm</td><td colspan="3"></td></tr><tr><td>DISTANCE</td><td></td><td colspan="3"></td></tr><tr><td>X.</td><td>±0.30</td><td>DRAWN</td><td>TONY</td><td>TITLE : TYPE-C 16PIN 单排 沉板1.0mm L=6.5mm</td></tr><tr><td>.X</td><td>±0.25</td><td>CHECKED</td><td>JACK</td><td>PARTS NO. :</td></tr><tr><td>.XX</td><td>±0.15</td><td>APPROVE</td><td>DAVID</td><td>DWG NO. :</td></tr><tr><td>.XXX</td><td>±0.10</td><td></td><td></td><td>SIZE A4 SCALE 1:1 SHEET 1 of 1 REV. A</td></tr><tr><td>ANGLE</td><td></td><td></td><td></td><td></td></tr><tr><td>X°</td><td>±2°</td><td></td><td></td><td></td></tr><tr><td>.X°</td><td>±1°</td><td></td><td></td><td></td></tr><tr><td>.XX°</td><td>±0.5°</td><td></td><td></td><td></td></tr></table>				TOLERANCES 一般公差	UNIT : mm				DISTANCE					X.	±0.30	DRAWN	TONY	TITLE : TYPE-C 16PIN 单排 沉板1.0mm L=6.5mm	.X	±0.25	CHECKED	JACK	PARTS NO. :	.XX	±0.15	APPROVE	DAVID	DWG NO. :	.XXX	±0.10			SIZE A4 SCALE 1:1 SHEET 1 of 1 REV. A	ANGLE					X°	±2°				.X°	±1°				.XX°	±0.5°			
TOLERANCES 一般公差	UNIT : mm																																																											
DISTANCE																																																												
X.	±0.30	DRAWN	TONY	TITLE : TYPE-C 16PIN 单排 沉板1.0mm L=6.5mm																																																								
.X	±0.25	CHECKED	JACK	PARTS NO. :																																																								
.XX	±0.15	APPROVE	DAVID	DWG NO. :																																																								
.XXX	±0.10			SIZE A4 SCALE 1:1 SHEET 1 of 1 REV. A																																																								
ANGLE																																																												
X°	±2°																																																											
.X°	±1°																																																											
.XX°	±0.5°																																																											
JSJ_frame_C Rev. A 2016/08/17										10																																																		

