






Circuit diagram



Product No. : TS-085S-□ □

型号: _____ : 包装方式
-P=编带(非编带, 不启用)

操作力度：
180=180gf±50gf
250=250gf±50gf



PCB Layout(Pattern Side)

(F)	Dust film		1	Polyimide tape	
(E)	Terminal		4	Phosphor bronze	Silvering
(D)	Reed		2	SUS	Silver covered
(C)	Base		1	LCP	Black
(B)	Cover		1	SUS	Natural
(A)	Keystoke		1	PPA	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI® Zhongdi Electronic Technology Co., Ltd

design		date		name	TACT SWITCHS
Review		date			
Approved		date		model	TS-085S-□
number:					

modify	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gape number		A4	
--------	--------	----------	-------------------------	------------	-----	------	----	-------------	--	----	---

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
机械性能 Mechanical Properties	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
	机械寿命 Mechanical life:	100,000 cycles Min
环境性能 Environmental	操作行程 Operation Stroke:	0.25±0.10mm
	工作温度 Operation temperature:	-25℃~ +75℃
可靠性特性 Reliability Characteristics	使用湿度 Use humidity:	≤85% RH
	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
应用领域 Application area	手工焊 Manual welding:	≥260℃ 时间 Time 3s
	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪




直流低电阻测试仪




耐电压测试



回流焊



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪										Zhongdi Electronic Technology Co., Ltd									
design			date			name			TACT SWITCHS										
Review			date																
Approved			date																
number:						model			TS-085S-□										
1:1		unit		mm		gape number								A4					