


Rev No.	Description of Revision	Date	Name	Approved	ECN No.
A					

- NOTES:
- 1.MATERIAL:
MOLDING: LCP UL94 V-0
CONTACT:COPPER ALLOY.
GOLD PLATED Min ON CONTACT AREA,100u”
Min TIN (LEAD FREE) ON SOLDER AREA,
SHELL: SUS201-H,T=0.25±0.02mm
50u” NICKEL PLATING OVER ALL.
 - 2.MECHANICAL:
INSERTION: 5~20N.
EXTRACTION: 8~20N AFTER TEST.
DURABILITY: 5000 CYCLES
 - 3.ELECTRICAL:
CURRENT: 3A FOR VBUS;
1.25A FOR GND PIN.
0.25A FOR OTHER.
VOLTAGE: 20 V MAX
WITHSTANDING VOLTAGE: 100V AC R.M.S.
CONTACT RESISTANCE: 40mΩ MAX.
INSULATION RESISTANCE: 100MΩ MIN.
 - 4.ENVIRONMENTAL
TEMPERATURE RANGE -25°C ~ +85°C



B12	GND
B9	VBUS
B5	CC2
A5	CC1
A9	VBUS
A12	GND
PIN	SIGNAL NAME

UNLESS OTHERWISE SPECIFIED TOLERANCES		浙江创都电子科技有限公司			
DECIMALS:		ANGLES		TITLE	
X.	±0.20	X°.	±2°	3. 1TYPE-C-6PH8. 8-LT-3J	
X.X	±0.10	X.X°	±1°	Drwn. JACK.LI	PART NO.
X.XX	±0.05	X.XX°	±0.5°	Checked. PETER.LIU	SCALE. 1:5
X.XXX	±0.03			Approved. LIJINYOU	UNIT. mm
				SIZE. A4	PROJ.
				SHEET. 2 OF 2	REV. A
CUSTOMER COPY					