









PIN NO.	NAME	YTYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)

Specification:


- 1.Electrical Characteristics:
Contact Current Rating:0.5 Amperes.
Dielectric Withstanding Voltage:AC500V r.m.s.
Insulation Resistance:1000 MΩ Minimum.
Contact Resistance:40 mΩ Maximum.
- 2.Environmental:
Operating Temperature:-25°C~+90°C.
- 3.Environmental:
Mating Cycles:5,000 Insertions.
- 4.Mechanical Characteristics:
Card Push Insertion/Out Force:0.2~1.40kgf.
Contact Separation Force:0.20kgf Minimum.
- 5.Material:
Insulator:HI-Temp Plastic UL 94V-0 Rated.
Contact:Copper Alloy(t=0.15mm).
Shell:Stainless Steel(t=0.15mm).
Spring:SWP.



RECOMMENDED P.C.B HOLE LAYOUT
COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)



CUSTOMER		GENERAL TOLERANCES UNLESS SPECIFIED		APPROVED BY: Song	TITLE: TF-CARD 03	深圳市辉焕科技有限公司	
SIZE A4	UNITS MM[INCH]	X±0.50	X'±5.0°	CHECKED BY: Talen	PART NO.: See the List		
SCALE 1:1	REV. D	.XX±0.25	.XX'±2.5°	DESIGN BY: Chen	DWG NO.:	SHEET 1/2	
		.XXX±0.15	.XXX'±2.0°				

RoHS



PACK DIRECTION

Product Direction



- 说明:
1. 每卷前后各空10PCS, 尾部用美纹胶纸封住;
 2. 将产品放满盘后, 再卷一圈保护带, 用美纹胶纸将其封住, 并贴上1Pcs物料标签;
 3. 每10卷盘一叠共10000Pcs装入1个外箱内;
 4. 在搬运过程中要轻拿轻放;
 5. 在运输中不可堆放过多(1.8M最高), 不可重压;

NO.	NAME	SPEC	Q' TY
①	FG RECEPTACLE		10000PCS/CARTON
①	CARRIER TAPE	W=24. 0mm, T=0. 30mm	1000PCS/PLATE
②	COVER TAPE	W=21. 3mm	10PLATES/CARTON
③	REEL PLATE		10PCS/CARTON
④	RoHS LABEL		10PCS/CARTON
⑤	PRODUCT LABER		10PCS/CARTON
⑥	CARTON	350*340*310mm	1PCS/PACKAGE

PACKAGING		GENERAL TOLERANCES UNLESS SPECIFIED		APPROVED BY:	TITLE:	深圳市辉焕科技有限公司	
SIZE	UNITS	X $\pm$ 1.0	X' $\pm$ 5.0'	Song	TF-CARD 03		
A4	MM[INCH]	.X $\pm$ 0.50	.X' $\pm$ 3.5'	CHECKED BY:	PART NO.:	SHEET	
SCALE	REV.	.XX $\pm$ 0.30	.XX' $\pm$ 2.5'	Talen	See the List		
1:1	1	.XXX $\pm$ 0.15	.XXX' $\pm$ 1.5'	DESIGN BY:	DWG NO.:	2/2	
				Chen			

