



防护等级 (Ingress protection)	IP50
插拔测试 (Plugging and unplugging test)	<2000次
产品耐温 (The product is temperature resistant)	-45° C / +135° C
盐雾腐蚀 (Salt Spray Corrosion)	>72 hr
测试电压 (kV rms) 针芯-针芯	1.2
额定电流Current rating	10A
电线尺寸Wire size	28-20AWG
导体接触规格 Conductor contact specifications	Ø1.3

外壳材料 Housing material	PC
绝缘体材料 Insulator material	PPS（可选PEEK） PPS（optional PEEK）
触体材料 Contact material	锡青铜镀金Contact material