




|                 |     |                           |      |                                                                                                   |                                                                                       |             |  |            |    |              |          |
|-----------------|-----|---------------------------|------|---------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------|--|------------|----|--------------|----------|
| 单位<br>UNIT      | mm  | 一般公差<br>GENERAL TOLERANCE |      | <div><div><div><div></div><div>首韩</div><div>SHOUHAN</div></div><div>深圳市首韩科技有限公司</div></div></div> |                                                                                       |             |  |            |    |              |          |
| 制图<br>DRAW      | 李春风 | L≤4                       | ±0.2 | 63<L≤250                                                                                          | ±0.5                                                                                  |             |  |            |    |              |          |
|                 |     | 4<L≤16                    | ±0.3 | 250<L                                                                                             | ±0.7                                                                                  |             |  |            |    |              |          |
|                 |     | 16<L≤63                   | ±0.4 | 角度 ANGULAR DIMENSION<br>±0.5°                                                                     |                                                                                       |             |  |            |    |              |          |
| 设计<br>DESIGN    |     |                           |      | 名称<br>NAME                                                                                        | 轻触开关                                                                                  |             |  |            |    |              |          |
| 审核<br>CHECKED   | 钟华华 | 材质<br>MATERIAL            |      | 型号<br>Model No.                                                                                   | TS667TP 250gf 013                                                                     |             |  |            |    |              |          |
| 标准化<br>STANDARD |     | 重量<br>WT.                 |      | 料号<br>Part No.                                                                                    |                                                                                       |             |  |            |    | 张数<br>SHEET  | 第1页, 共1页 |
| 批准<br>APPROVE   | 罗孝金 | 表面积<br>SA.                |      | 视角<br>PROJ.                                                                                       |  | 比例<br>SCALE |  | 版本<br>REV. | A4 | C 图<br>C DWG |          |



深圳市首韩科技有限公司

SHENZHEN SHOUHAN TECHNOLOGY CO., LTD

Tel: 0755-27597601 Fax: 0755-27597491

## 承 认 书

### SPECIFICATION FOR APPROVAL

产 品 编 码

Material code:

产品名称 Project:

轻触开关

规格型号 Part No:

TS667TP 250gf 013

贵公司承认印 Approval signatures

| 料 号/Part No. | 签 章/Signatures |
|--------------|----------------|
|              |                |

日期 Date:

|             |     |                                                                                      |
|-------------|-----|--------------------------------------------------------------------------------------|
| 拟制/Drawn    | 李春风 |  |
| 审核/Check    | 钟华华 |                                                                                      |
| 批准/Approved | 罗孝金 |                                                                                      |

## 产 品 规 格 书

### PRODUCT SPECIFICATION

|                               |                                    |                                                                                                                                                                     |                                                                                    |
|-------------------------------|------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|
| SIRLES                        |                                    | 系列:FLIP SWITCHES(轻触开关)                                                                                                                                              |                                                                                    |
| MODEL                         |                                    | 型号: TS667TP 250gf 013                                                                                                                                               |                                                                                    |
| 1.RATING                      |                                    | 额定值:50mA 12VDC                                                                                                                                                      |                                                                                    |
| 2.CONSTRUTION DIMENSION 结构尺寸  |                                    | Apply to the appended drawing符合附加图纸                                                                                                                                 |                                                                                    |
| 3.APPEARANCE 外观               |                                    | Have no remarkable damage,crack and rust etc无<br>明显损伤,裂纹,锈迹等.                                                                                                       |                                                                                    |
| 4.CONTACTLOOP 接触回路            |                                    | Monople loop:单通单极回路                                                                                                                                                 |                                                                                    |
| ITEM 专案                       |                                    | TEST CONDITION 测试条件                                                                                                                                                 | SPECIFICATION 规格                                                                   |
| 5.CAPABILITY OF ELECTRIC 电气性能 |                                    |                                                                                                                                                                     |                                                                                    |
| 5A                            | INSULATION RESISTANCE<br>绝缘电阻      | Measurements shall be made following Application of DC500V potential across terminals and across terminals and fuame for 1minute在端子之间和端子与壳之间加 DC500V 条件下,持续 1 分钟测量. | 100M $\Omega$ min<br>100 兆欧以上.                                                     |
| 5B                            | WITHSTAND VILTAGE<br>耐电压           | AC250V、50HZ、1 min (imin(interrupting current $\leq$ 500uA). AC250V、50HZ、1 分钟(漏电流 500uA)                                                                             | There shall be no briakdown 无击穿现象出现。                                               |
| 5C                            | CONTACT CIRCUIT<br>接触电路            | Addition 1.5-2 time force on the top of the keystrok and press the switch,DC50V100mA在按键顶端上等于作用力 1.5-2 倍的力按动开关,DC50V,10Ma.                                           | 100m $\Omega$ Max<br>(100 m $\Omega$ 以下) .                                         |
| 5D                            | SWITCH CONNECTION<br>FLASH 开关接触点抖动 | Addition DC5V on the two side of switch,at a speed of 3-5time a sec.to press the switch在开关的两端加 DC5V 的电压,以 3-5 次/秒的速度按动开关.                                           | The flash time between open not more than 10ms.<br>开关在接通和断开时的接点抖动时间不大于 10 ms.      |
| 6.MECHANICAL EFFICIENCY 机械性能  |                                    |                                                                                                                                                                     |                                                                                    |
| 6A                            | CONTACT STRENGTH<br>按键强度           | The contact shall be capable of a rorce of 5N for 5 seconds in any directions沿开关动作方向可承受静能压力 5N, 保持 5 秒钟.                                                            | Switch electric andmechanical efficiency does not break 无损开关电气或者机械性能               |
| 6B                            | CONTACT JOURNEY                    |                                                                                                                                                                     | 按键行程:0.25 $\pm$ 0.1mm                                                              |
| 6C                            | DRIVE FORCE<br>驱动力                 | Being measure at across spring piece and across keystoke forergometer用测力计在按键与弹片之间测量.                                                                                | Contact switch'sd drive dirive fouce was250 $\pm$ 50gf.<br>按键的开关驱动力为250 $\pm$ 50gf |

## 产 品 规 格 书

### PRODUCT SPECIFICATION

- 2 -

|                                             |                                                                                                                                                                                                                                      |                                                                                                                                                                                |                                                                                                                                            |
|---------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| 6D                                          | CONNECTION STRENGTH<br>接线端强度                                                                                                                                                                                                         | A force of 1N being applying in any directions of the switch connection partt.在接线端的作用方向施加 1N 的力.                                                                               | Switch mechanical efficiency does not break.无损开关机械性能.                                                                                      |
| 6E                                          | MECHANICAL LIFE<br>机械寿命                                                                                                                                                                                                              | Operatin at a rate of 30-50 cycles a minute. 以 30-50 次/分的驱动速度操作.                                                                                                               | Life:100000cycles<br>寿命:100000 次                                                                                                           |
| 7.ENVIRONME NT---RESISTANT EFFICIENCY 耐环境性能 |                                                                                                                                                                                                                                      |                                                                                                                                                                                |                                                                                                                                            |
| 7A                                          | CHANGE OF TEMPERATURE 温度变化                                                                                                                                                                                                           | The first temperature shall be 65℃ ,2h and changed to-30℃ ,2h,5c ycles of above test . 先 65℃ ,2h,然后 -30℃ ,2h, 如此重复 3 次.                                                        | 1. The appearance should not break. 外观应无损伤.<br>2. Contact resistance $\leq 100 \text{ M } \Omega$ 接触电阻 $\leq 100 \text{ M } \Omega$        |
| 7B                                          | HUMIDITY RESISTANT 耐湿热                                                                                                                                                                                                               | 40 $\pm$ 2℃ in temperature and 95%RH ,Ruring the test time without load; After testing the temperature should be 48h. 经 40 $\pm$ 2℃ ,相对湿度 95% , 试验期间,开关不动作,不带电负荷,试验后恢复到常温 48h. | 3. Insulation resistance $\geq 100 \text{ M } \Omega$ . 绝缘电阻 $\geq 100 \text{ M } \Omega$                                                  |
| 8.IOINTING EFFICIENCY 焊接性能                  |                                                                                                                                                                                                                                      |                                                                                                                                                                                |                                                                                                                                            |
| 8A                                          | SOLDERABILITY<br>可焊性                                                                                                                                                                                                                 | Temperature260 $\pm$ 5℃ ;Duration;3 $\pm$ 0.5S:温度在 260 $\pm$ 5℃ ,持续 3 $\pm$ 0.5S.                                                                                              | Solderability part should above 90% 可焊部分被焊料覆盖面应在 90% 以上.                                                                                   |
| 8B                                          | SOLDER—RESISTANT<br>耐焊剂性                                                                                                                                                                                                             | Warm-up temperature:100℃,40S,焊锡温度 260 $\pm$ 5℃ ,浸焊时间 3 $\pm$ 0.5S.                                                                                                             | Froth height of assist solder should under board and switch electric and mechanical efficiency does not break.助焊剂发泡不应超过印制板,无损伤开关电气或机械动作性能. |
| 8C                                          | JOINTING—RESISTANT<br>耐焊接热                                                                                                                                                                                                           | Jointing temperature: 260 $\pm$ 5℃ ,Duration of immersion: 5 $\pm$ 1S.焊锡温度 260 $\pm$ 5℃ ,浸焊时间5 $\pm$ 1S                                                                        | efficiency does not break 无损伤开关电气或机械动作性能.                                                                                                  |
| 8D                                          | NORMAL JOLNTING TIMES<br>正常焊接次数                                                                                                                                                                                                      |                                                                                                                                                                                | $\leq 2$ times 小于 2 次                                                                                                                      |
| 9.NOTES                                     |                                                                                                                                                                                                                                      |                                                                                                                                                                                |                                                                                                                                            |
| 9A                                          | The whole boxes of switch should keep in the temperature -30--80℃ and less than 80%RH withort acidic,alkalescence,caustic gas in the environment of the storage.<br>整箱包装的开关,应在温度为-30--80℃ ,相对湿度不大于 80% ,周围的空气中没有酸性、碱性或其他腐蚀性气体的库房内保管。 |                                                                                                                                                                                |                                                                                                                                            |
| 9B                                          | Operating Temperature Range:-25 to 70℃<br>操作温度的范围: -25 to 70℃                                                                                                                                                                        |                                                                                                                                                                                |                                                                                                                                            |
| 9C                                          | Switch should install in a correct method.<br>开关应按正确的安装方法进行正确安装使用。                                                                                                                                                                   |                                                                                                                                                                                |                                                                                                                                            |