










SUGGESTED PCB LAYOUT
(COMPONENT SIDE)



2P外观

REV.	DESCRIPTION	DATE
A/0	新版发行	2022.11.28
B/0	升 B 版	2024.8.14

技术参数:

- 所有材料符合ROHS2.0/REACH/HF要求。
- 额定电流: 2A, AC, DC;
- 额定电压: 250V, AC, DC;
- 温度范围: -25℃~+85℃;
- 接触电阻: $\leq 0.03 \Omega$;
- 绝缘电阻: $\geq 1000M \Omega$;
- 耐压: 1000V, AC/minute.
- 产品料号:

A20002 - n AB - 03 T1
孔位
产品类型
AB: 立贴针座
电镀
T1: 镀亮锡
胶芯材质
03: LCP 本色

Circuits	Dimensions (mm)			
	A	B	C	D
02	2.00	4.80	8.00	2.45
03	4.00	6.80	10.00	3.00
04	6.00	8.80	12.00	5.00
05	8.00	10.80	14.00	7.00
06	10.00	12.80	16.00	9.00
07	12.00	14.80	18.00	11.00
08	14.00	16.80	20.00	13.00
09	16.00	18.80	22.00	15.00
10	18.00	20.80	24.00	17.00
11	20.00	22.80	26.00	19.00
12	22.00	24.80	28.00	21.00
13	24.00	26.80	30.00	23.00
...	...	...	...	...
16	30.00	32.80	36.00	29.00

4	吸盖 Cap	LCP (UL94V-0)	1	本色
3	焊片 Fitting Nail	黄铜 Brass	2	电镀(锡): 整个表面镀底锡30u"MIN, 再镀锡80u". MIN.
2	端子 Contact	黄铜 Brass	n*1	电镀(锡): 整个表面镀底锡30u"MIN, 再镀锡80u". MIN.
1	基座 Wafer	LCP (UL94V-0)	1	本色
序号	名称	材料	数量	附注

GENERAL TOLERANCES				DRAWN BY	罗荣程/2024.8.14		浙江深海电子有限公司		
0.X	±0.25	X.°	±3°	CHK. BY	朱江浩/2024.8.14				
0.XX	±0.12								
0.XXX	±0.05	X.X°	±0.5°	APRV. BY	姚 涛/2024.8.14				
UNIT	SIZE	SCALE		DRAWING NO.	SHEET	PROD. NAME SH-HY2.0-NALT			
MM	A4	1:1		H20011-00	1 OF 1	PART NO. A20002-nAB-03T1			
				TITLE 2.0mm pitch 180° WAFER-SMT TYPE					