




RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2025.12.20




- NOTES:
- MATERIAL:
HOUSING:LCP S475 UL 94V-0
CONTACT:C5191
SHELL:SUS304-H
 - FINISH:
CONTACT:GOLD FLASH PLATED ON CONTACT AREA
GOLD FLASH PLATED ON SOLDER TAILS
 - ELECTRICAL CHARACTERISTICS
RATING CURRENT : 0.5A MAX
CONTACT RESISTANCE :50 mΩ MAX
DIELECTRIC WITHSTANDING : 500V AC MIN
INSULATION RESISTANCE: 1000 MΩ MIN
 - MECHANICAL CHARACTERISTICS
MATING CYCLE :3000 CYCLES

SIM pin Assignment	
PIN#	Name
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O


THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO:		MIS11-S1F1-2000-A		XFCN 兴飞连接器		
TITLE: MICRO SIM PUSN卡座 (无CD)				0769-82001899		
				www.xfconn.com		
				DWG NO: /		
APPD	Chen ZhiQiang					
CHKD	Liu Wei			VIEW		
DRAW	Chen HongJiang			SCALE	SHEET	REV
DATE	2025.12.20			NONE	1/2	A1

RoHS






COVER TAPE PEELING FORCE:50gf-150gf



- 1.依(图一) 示放置产品于下载中，每穴放置1PCS产品。
- 2.包装机包好后，在REEL的等分点贴上胶带，以防止 REEL张开，每REEL贴1PCS标签，
- 3.包装数量见如TABLE 1
- 4.包装成箱见如图三
箱底放保丽龙板，在依次将指定数量卷装放入箱内，四角分别放入四个三角护板，最上层再放保丽龙板。
- 5.封箱，在封好的纸箱上按客户要求写上料号，数量等。

REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2025.12.20

QTY/REEL	REEL/CARTON	QTY/CARTON
1200	10	12000



X. 0. 3	X. ° ±	PART NO: MIS11-S1F1-2000-A		XFCN 兴飞连接器	
. X ± 0. 2	. X ° ±	TITLE: MICRO SIM PUSN卡座 (无CD)		0769-82001899	
. XX ± 0. 08	. XX ° ±			www.xfconn.com	
. XXX ± 0. 03	. XXX ° ±			DWG NO: /	
UNITS:	mm	APPD	Chen ZhiQiang	VIEW	⊕
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		CHKD	Liu Wei	SCALE	SHEET
		DRAW	Chen HongJiang		REV
		DATE	2025.12.20	NONE	2/2
					A1