





P/N	PIN	DIM.A	DIM.B
PM-2.54-2*01-8.5-ZZ	2*1	0.00	2.54
PM-2.54-2*02-8.5-ZZ	2*2	2.54	5.08
PM-2.54-2*03-8.5-ZZ	2*3	5.08	7.62
PM-2.54-2*04-8.5-ZZ	2*4	7.62	10.16
PM-2.54-2*05-8.5-ZZ	2*5	10.16	12.70
PM-2.54-2*06-8.5-ZZ	2*6	12.70	15.24
PM-2.54-2*07-8.5-ZZ	2*7	15.24	17.78
PM-2.54-2*08-8.5-ZZ	2*8	17.78	20.32
PM-2.54-2*09-8.5-ZZ	2*9	20.32	22.86
.....			
PM-2.54-2*40-8.5-ZZ	2*40	(PIN-1)X2.54	(PIN)X2.54

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM.	TOL.	TITLE: 2.54FH H8.5 2xnPin 180度 Y型 PC3.2 6T					
x.	±0.30						
x.x	±0.20						
x.xx	±0.10						
GENERAL ANGLE:		DWG. NO.: PM-2.54-2*N-8.5-ZZ		CHECKED: MAX			
x°	±5°	PART NO.: PM-2.54-2*N-8.5-ZZ		DRAWN: ELLA			
x.x°	±1°						
x.xx°	±0.5°						
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL