



[Schematic]



[P.C.B.LAYOUT]

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

1.Specification:

- 1>.Operation force: 1000gf Max.
- 2>.Operation Temperature: -30°C to $+85^{\circ}\text{C}$.
- 3>.Storage Temperature: -40°C to $+85^{\circ}\text{C}$.
- 4>.Mechanical Life: 1000 cycles operations.
- 5>.Resistance to Soldering: $260\pm 5^{\circ}\text{C}$ for 3-5 Seconds.


2.PLATING:

- 1>.GOLD flash 1u"(min) SOLDER TAIL,
3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

- 1>.Non-switch Rating: 100mA at 50V DC.
- 2>.Switching Rating: 25mA at 24V DC.
- 3>.Contact Resistance: Initial 50m Ω Max.
Contact Resistance: After life 100m Ω Max.
- 4>.Insulation Resistance: 100M Ω Min at 100VDC.
- 5>.Dielectric Strength: 300V AC for 60seconds.
- 6>.Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:



5.PACKING: 2000pcs/Reel/Box.

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
>0 $\pm$ 0.05 >1 $\pm$ 0.10 >10 $\pm$ 0.30	>0 $\pm$ 0.5° >5 $\pm$ 1.0°	PART NO.	TITLE: PRODUCT Family DSHP		
		DSHP10TJGER	Series Pitch 1.27mm		
		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	---	APPD: Ava		N:A	1/1