

SPECIFICATION FOR APPROVAL

承认试样书

Schottky Barrier Rectifiers

制品品名 (P/N): GD MBRF1040CT

SUZHOU GOOD-ARK ELECTRONICS CO.,LTD.

贵公司承认栏 (CONFIRMATION)

承认章 (STAMP)

CHECK BY	EXAMINED BY	APPROVED BY




Product Specification

GOODARK Type

MBRF1040CT

Construction : Schottky Barrier Rectifier
Application : For General Purpose
(Manufacturer) :
Suzhou Goodark Electronics Co.,Ltd
Prepared on Aug. 19th, 2011
Prepared: R & D Department
Approval : QRA Department



1. Anode 2. Cathode 3. Anode


**SCHOTTKY BARRIER
RECTIFIER
10 AMPERES
40VOLTS**

CONTENTS

1. Package Outline
2. Marking
3. Features& Mechanical Characteristics
4. Maximum Ratings and Electrical Characteristics
5. Rating and characteristic Curves
6. Packing Specification PACKAGING SPECIFICATION
7. Description of Box Label

1. Package Outline (TO220F-AB)


UNIT:mm



Lead Frame Material : Copper Plating: Pure Tin Plating

Plating Thickness : $8\mu\text{m}$ to $25.4\mu\text{m}$

2.MARKING



1. Part Name : MBRF1040CT

2. Logo Mark: 

3. Polarity : 



3.Features& Mechanical Characteristics

Features

- Plastic package has underwriters Laboratory
Flammability Classification 94V-0
- Dual rectifier construction, positive center tap
- Metal of silicon rectifier, majority carrier conduction
- Low forward voltage, high efficiency
- Guarding for over voltage protection
- For use in low voltage, high frequency inverters,
- Free wheeling, and polarity protection applications

Mechanical Characteristics

- Case : Epoxy, Molded
- Weight: 1.9grams (approximately)
- Finish : All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes : 260°C Max.for10 sec
- Shipped 50 units per plastic tube

4.Maximum Ratings and Electrical Characteristics

MAXIMUM RATINGS and ELECTRICAL CHARACTERISTICS(TC=25°C unless otherwise moted)					
PARAMETER	TEST CONDITIONS		SYMBOL	MBRF1040CT	UNIT
Maximum repetitive peak reverse voltage			VRRM	40	V
Working peak reverse voltage			VRWM	40	V
Maximum DC blocking voltage			VDC	40	V
Maximum average forward rectified current at Tc=105°C total device per diode			IF(AV)	10 5.0	A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load per diode			IFSM	125	A
Peak repetitive reverse current per leg at tp=2.0us , 1KHz			IRRM	0.5	A
Isolation voltage (TO220F-AB only) from terminal to heatsink t = 1 min			VAC	1500	V
Voltage rate of change (rated VR)			DV/dt	10000	V/us
Operating junction temperature range			TJ	—55 to +150	°C
Storage temperature range			TSTG	—55 to +150	°C
Maximum instantaneous forward voltage per leg	IF=5.0A IF=5.0A	Tc=25°C Tc=125°C	VF	0.70 0.57	V
Maximum reverse current per leg at working peak Reverse voltage		Tj=25°C Tj=100°C	IR	100 10.0	uA mA

Thermal Characteristics Ta=25°C unless otherwise noted

Symbol	Parameter	Max	Unit
RθJC	Thermal Resistance, Junction to Case per Leg	2.0	°C/W
RθJA	Thermal Resistance, Junction to Ambient per Leg	62.5	°C/W

Note :

1. Screw mounting with 4-40 screw, where washer diameter is ≤4.9mm(0.19")
2. Pulse test:300us pulse width,1% duty cycle

5. Rating and Characteristic Curves

Rating and Characteristic Curves

($T_c=25^\circ\text{C}$ unless otherwise noted)




Fig. 1 Forward Current Derating Curve




Fig. 2 Typical Forward Characteristics




Fig. 3 Max Non-Repetitive Surge Current







Fig. 4 Typical Junction Capacitance

6. Packing Specification

	
1) Tube : 50units	2) Inner Box: 20 tube(1000units)
	
3) Outer Box: 10 inner box (10,000units)	

7. DESCRIPTION of BOX LABEL

	
1) Inner Box Label	2) Inner Box Label
	
3) Outer Box Label	4) Outer Box Label