



钛迪半导体
Tudi Semiconductor

Tudi Semiconductor

Product Specification

TUDI-ICL3232

±15 kV ESD Protected, 3.3 V, RS-232 Line Driver/Receiver

网址 www.sztbdbdt.com 

用芯智造 · 卓越品质

**semiconductor device
manufacturer**

- Design
- research and development
- production
- and sales



Features

- Complies with the RoHS directive
- 15kV ESD protection (Human model)
- ICL3232 offers power consumption and pin compatibility with competitive devices
- Compatible with RS-232, VCC = 2.7V
- Complies with EIA/IA-232 and V.28/V.24 specifications, voltage = 3V
- No lock effect
- On-chip voltage translator requires only external 0.1 μ F capacitors
- Receiver hysteresis effect, improves noise immunity
- Data rate 250kbps
- Wide supply range single 3V to 5.5V
- Supply current in shutdown mode: 1 μ A




Figure 1. Pin Diagram

Description

The ICL3232 devices is 3.0V to 5.5V powered RS-232 transmitters/receivers that meet EIA/TIA-232 and V.28/V.24 specifications, even at VCC = 3.0V.

Targeted applications are PDAs, notebook, and laptop computers where the low operational power consumption and even lower standby power consumption are critical. Reduce the standby supply current to a 1 μ A trickle. Small footprint packaging, and the use of small, low value capacitors ensure board space savings as well.

The data rates is 250kbps . This family is fully compatible with 3.3V only systems, mixed 3.3V and 5.0V systems, and 5.0V only systems.

Applications

- Any system requiring RS-232 communication ports
- Battery powered, hand-held, and portable equipment
- Laptop computers, Notebooks
- Modems, printers, and other peripherals
- Digital cameras
- Cellular/mobile phones



Pin description

PIN	SYMBOL	DESCRIPTION
1	C1+	Positive Terminal for the first Charge Pump Capacitor
2	V+	Doubled Voltage Terminal
3	C1-	Negative Terminal for the first Charge Pump Capacitor
4	C2+	Positive Terminal for the second Charge Pump Capacitor
5	C2-	Negative Terminal for the second Charge Pump Capacitor
6	V-	Inverted Voltage Terminal
7	T2OUT	Second Transmitter Output Voltage
8	R2IN	Second Receiver Input Voltage
9	R2OUT	Second Receiver Output Voltage
10	T2IN	Second Transmitter Input Voltage
11	T1IN	First Transmitter Input Voltage
12	R1OUT	First Receiver Output Voltage
13	R1IN	First Receiver Input Voltage
14	T10UT	First Transmitter Output Voltage
15	GND	Ground
16	VCC	Supply Voltage



Parameter limit

PARAMETER	SYMBOL	VALUE	UNIT
Supply voltage	VCC	-0.3~+6	V
Doubled Voltage Terminal	V+	VCC-0.3~+7	V
Inverted Voltage Terminal	V-	+0.3~-7	V
V++ V-		+13	V
Transmitter Input Voltage Range	T1IN,T2IN	-0.3~+6	V
Receiver Input Voltage Range	R1IN,R2IN	±25	V
Transmitter Output Voltage Range	T1OUT,T2OUT	±13.2	V
Receiver Output Voltage Range	R10UT,R2OUT	-0.3~VCC+0.3	V
Operating Temperature		-40~85	°C
Storage Temperature		-60~150	°C
Soldering Temperature		300	°C
Continuous Power	SOP16	760	mW
	DIP16	840	mW

The maximum limit parameters means that exceeding these values may cause irreversible damage to the device. Under these conditions, it is not conducive to the normal operation of the device. The continuous operation of the device at the maximum allowable rating may affect the reliability of the device. The reference point for all voltages is ground.

Logic Input Electrical Characteristics

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Logic Control Low Level	VTTIN_L	T1IN,T2IN			0.8	V
Logic Control High Level	VTTINH	T1IN,T2IN	2			V
Logic Control Hysteresis		T1IN,T2IN		0.3		V
Input Logic Current	ITIN	T1IN,T2IN			±1	µA

(If there is no additional explanation,typical value is tested when VCC=+3.3V,Temp=25 ,C1-C4=1 µF)



Receiver Output Electrical Characteristics

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Receiver Output Logic-Low Voltage	VROL	I _{OUT} =1.6mA, V _{CC} =5V or 3.3V			0.4	V
Receiver Output Logic-High Voltage	VROH	I _{OUT} =-0.5mA, V _{CC} =5V or 3.3V	V _{CC} -0.6	V _{CC} -0.1		V

(If there is no additional explanation,typical value is tested when V_{CC}=+3.3V,Temp=25°C,C1-C4=1μF)

Receiver Input Electrical Characteristics

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Receiver Input Range	VRIN		-25		+25	V
Receiver Input Low Threshold	VRL	V _{CC} =3.3V	0.6	1.1		V
		V _{CC} =5V	0.8	1.5		V
Receiver Input High Threshold	VRIH	V _{CC} =3.3V		1.5	2.4	V
		V _{CC} =5V		1.9	2.4	V
Receiver Input Hysteresis				0.4		V
Receiver Input Impedance	RRIN		3	5	7	kΩ

(If there is no additional explanation,typical value is tested when V_{CC}=+3.3V,Temp=25°C,C1-C4=1μF)

Transmitter Output Electrical Characteristics

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Transmitter Output Swing	VTOUT	All output ports of transmitter connect 3kΩload to ground	±4		±5	V
Transmitter Output Impedance	RTOUT	V _{CC} =0V, Transmitter Input=±2V	300			Ω
Transmitter Short-Circuit Current	Itsc				60	mA

(If there is no additional explanation,typical value is tested when V_{CC}=+3.3V,Temp=25°C,C1-C4=1μF)



Supply Current

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Supply Current with no Load	I_{sup}			2		mA

(If there is no additional explanation,typical value is tested when $VCC=+3.3V$,Temp=25°C,C1-C4=1μF)

ESD Protection

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
R1IN、R2IN T1OUT、T2OUT		HBM		±15		kV
		Air Discharge		±15		kV
		Contact Discharge		±8		kV

Switching Characteristics Parameter

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Rate	Speed	$RL=3k\Omega$, $CL=1000pF$		120		kbps
Receiver Propagation delay	tRPHL	$CL=150pF$		300		ns
	tRPLH			300		ns
$ tRPHL-tRPLH $				150		ns
$ tTPHL-tTPLH $				150		ns
Transmitter Slew Rate	SR	$RL=3k\Omega \sim 7k\Omega$, $CL=150pF \sim 1000pF$ from -3.0V ~ 3.0V or from 3.0V ~ -3.0V See figures 2 and 3	4		30	V/μs

(If there is no additional explanation,typical value is tested when $VCC=+3.3V$,Temp=25°C,C1-C4=1μF)



TEST CIRCUIT




Figure 2 minimum swing rate test circuit




Figure 3 maximum swing rate test circuit




Figure 4 ESD test model of human body mode




Figure 5 human body mode current waveform




Figure 6 ESD test model of IEC 1000-4-2




Figure 7 current waveform of IEC 1000-4-2 ESD



Description

RS232 Receiver

The 3232 has two separate receivers that convert the RS-232 signal to the CMOS logic output level.

ESD Protection

All pins of 3232 adopt ESD protection structure, and all driver outputs and receiver inputs have additional electrostatic protection capability. It can withstand $\pm 15\text{kV}$ ESD (HBM) discharge, contact discharge above $\pm 8\text{kV}$ and air gap discharge above $\pm 15\text{kV}$. The ESD protection structure can withstand the impact of high voltage ESD under all conditions, including standard working mode and power-off mode.

Typical Application

Typical dual-Path application scenarios are shown in Figure 8, where the C1-C5 typical capacitance value is $0.1\mu\text{F}$.

Dual Charge-Pump Operation

3232 has a two-way charge pump inside to support the chip's voltage conversion work. Dual-electric pump provides $+5.5\text{V}$ and -5.5V output voltage in the range of $3.0\text{-}5.5\text{V}$. Each charge pump requires a capacitor (C1, C2) and an energy storage capacitor (C3, C4) to generate V₊ and V₋ power supplies, as shown in Fig 8.

RS232 Transmitter

Convert the TTL/CMOS logic voltage to a voltage compatible with the EIA/TIA-232 standard. 3232 Transmitter can guarantee 250kbps data rate under the worst operating conditions (Parallel load of $3\text{k}\Omega$ resistor and 1000pf capacitor). Transmitter can drive multiple receivers in parallel. There is no pull-up resistance inside the input terminals T1IN and T2IN of 3232 transmitter. If the transmitter is not used, the unused input terminals T1IN and T2IN can be connected to GND or VCC.








Figure 8 Typical dual-Path application scenarios

Order information

Order Number	Package	Package Quantity	Marking On The park	Temperature
ICL3232CAZ-T-TUDI	SSOP16	Tape,Reel,2000	3232CAZ	0°C to 70°C
ICL3232CBZ-T-TUDI	SMD16	Tape,Reel,1000	3232CBZ	
ICL3232CBNZ-T-TUDI	SOP16	Tape,Reel,2500	3232CBNZ	
ICL3232CVZ-T-TUDI	TSSOP16	Tape,Reel,2500	3232CVZ	
ICL3232IAZ-T-TUDI	SSOP16	Tape,Reel,2000	3232IAZ	- 40°C to 85°C
ICL3232IBZ-T-TUDI	SMD16	Tape,Reel,1000	3232IBZ	
ICL3232IBNZ-T-TUDI	SOP16	Tape,Reel,2500	3232IBNZ	
ICL3232IVZ-T-TUDI	TSSOP16	Tape,Reel,2500	3232IVZ	






Package SSOP16




SIZE SYMBOL	MIN/mm	MAX/mm
A	6.15	6.25
A1	0.30TYP	
A2	0.65TYP	
A3	0.675TYP	
B	5.25	5.35
B1	7.65	7.95
B2	0.60	0.80
C	1.70	1.80
C1	1.75	1.95
C2	0.799	
C3	0.152	
C4	0.172	
H	0.05	0.15
θ	12°TYP4	
01	12°TYP4	
02	10°TYP	
03	0°~8°	
R	0.20°TYP	
R	0.15°TYP	



Package TSSOP16




SIZE SYMBOL	MIN./mm	TYP./mm	MAX./mm
A	--	--	1.20
A1	0.05		0.15
A2	0.90	1.00	1.05
b	0.20	--	0.30
b1	0.19	0.22	0.25
c	0.110	0.127	0.145
c1	0.12	0.13	0.14
D	4.86	4.96	5.06
E	6.20	6.40	6.60
E1	4.30	4.40	4.50
e		0.65BSC	
L	0.45	0.60	0.75
L1		1.00BSC	
	0°	--	8°






Package SOP16



SYMBOL	SIZE MIN./mm	SIZE MAX./mm
A	9.80	10.00
A1	0.356	0.456
A2	1.27TYP	
A3	0.302TYP	
B	3.85	3.95
B1	5.84	6.24
B2	5.00 TYP	
C	1.40	1.60
C1	0.61	0.71
C2	0.54	0.64
C3	0.05	0.25
C4	0.203	0.233
D	1.05 TYP	
D1	0.40	0.70
D2	0.15	0.25
R1	0.20TYP	
R2	0.20TYP	
01	8°~12°TYP4	
02	8°~12°TYP4	
03	0°~8°	
04	4°~12°	



Package SMD16



SYMBOL	SIZE MIN./mm	SIZE MAX./mm
A	—	2.65
A1	0.10	0.30
A2	2.25	2.35
A3	0.97	1.07
D	10.10	10.50
E	10.26	10.60
E1	7.30	7.70
e	1.27BSC	
L	0.55	0.85
L1	1.4BSC	
H	0.345	0.365
R	0.20TYP	
R1	0.30TYP	
θ	0°	8°
θ1	45° TYP	
θ2	12° TYP	
θ3	0°	8°
θ4	0°	10°



Important statement:

- TUDI Semiconductor reserves the right to modify the product manual without prior notice! Before placing an order, customers need to confirm whether the obtained information is the latest version and verify the completeness of the relevant information.
- Any semi-guide product is subject to failure or malfunction under specified conditions. It is the buyer's responsibility to comply with safety standards when using TUDI Semiconductor products for system design and whole machine manufacturing. And take the appropriate safety measures to avoid the potential risk of loss of personal injury or loss of property situation!
- TUDI Semiconductor products have not been licensed for life support, military, and aerospace applications, and therefore TUDI Semiconductor is not responsible for any consequences arising from the use of this product in these areas.
- If any or all TUDI Semiconductor products (including technical data, services) described or contained in this document are subject to any applicable local export control laws and regulations, they may not be exported without an export license from the relevant authorities in accordance with such laws.
- The specifications of any and all TUDI Semiconductor products described or contained in this document specify the performance, characteristics, and functionality of said products in their standalone state, but do not guarantee the performance, characteristics, and functionality of said products installed in Customer's products or equipment. In order to verify symptoms and conditions that cannot be evaluated in a standalone device, the Customer should ultimately evaluate and test the device installed in the Customer's product device.
- TUDI Semiconductor documentation is only allowed to be copied without any alteration of the content and with the relevant authorization. TUDI Semiconductor assumes no responsibility or liability for altered documents.
- TUDI Semiconductor is committed to becoming the preferred semiconductor brand for customers, and TUDI Semiconductor will strive to provide customers with better performance and better quality products.