

深圳市索瑞达电子有限公司

承 认 书

SPECIFICATION FOR APPROVAL

客 户 名 称: _____ 标准
Customer Name : _____

客 户 料 号 : _____
Customer P/N: _____

产 品 名 称: _____ 功率电感
Product Name: _____

索 瑞 达 料 号: _____ SRYH.1050.YF系列
Sorede P/N: _____

制造厂商 Manufacturer	
拟 制 Draft	唐杨英
审 核 Check	工程专用章 符妃团
日 期 Date	2022-02-21

客户承认印章 Approval Signet	
日 期 Date	

地址:深圳市观澜镇福城街道新塘村8号源创园陆号A6栋3楼.

Address:3Rd Floor, Building A6, Yuanchuangyuanlu, No. 8 Xintang Village,
Fucheng Street, Guanlan Town, Shenzhen.



电话 Tel: 0755-29803356 传真 Fax: 0755-29803506

电子邮件 E-mail: sorde@vip.163.com

网址 http:// www.szsorede.com

Modify Resume


A

文件编号 File Number	SRD-WI-15603	版本号 Version Number	A	页码 page	1/8																
1、外形尺寸 Dimension：				单位Unit: mm																	
				<table><tr><td>A</td><td>11.0±0.5</td></tr><tr><td>B</td><td>10.0±0.3</td></tr><tr><td>C</td><td>5.0MAX</td></tr><tr><td>D</td><td>2.0±0.5</td></tr><tr><td>E</td><td>3.0±0.3</td></tr><tr><td>F</td><td>4.1Ref</td></tr><tr><td>G</td><td>13.6Ref</td></tr><tr><td>H</td><td>5.4Ref</td></tr></table>		A	11.0±0.5	B	10.0±0.3	C	5.0MAX	D	2.0±0.5	E	3.0±0.3	F	4.1Ref	G	13.6Ref	H	5.4Ref
A	11.0±0.5																				
B	10.0±0.3																				
C	5.0MAX																				
D	2.0±0.5																				
E	3.0±0.3																				
F	4.1Ref																				
G	13.6Ref																				
H	5.4Ref																				
2、产品品名构成 Product Spec. Model																					
SRYH . 1050 . Y F 2R2 M T 00 a b c d e f g h																					
a: 系列名称Series name																					
b: 产品尺寸Product dimensions（A x B x C）																					
c: 密封方式Sealing way (L: 冷封Cold seal Y: 热封Heat seal)																					
d: 印字方向 Lettering direction ▶																					
e: 电感值Inductance Value																					
(1R0:1.0uH; 100: 10uH; 101:100uH)																					
f: 电感公差Inductance Tolerance (K:10% ; M:20% ; N:30%)																					
g: 包装Package(T:磁带/卷轴Tape/Reel、B: 散装Bulk)																					
h: 编号Numbering（标准standard）																					
3、材料清单MATERIAL LIST																					
NO.	PARTS	MATERIAL	UL FILE NO.	TEMP. CLASS																	
1	Iron Powder	ALLOY OR EQUIVALENT	NA	NA																	
2	WIRE	POLYURETHANE ENAMELLED COPPER WIRE OR EQUIVALENT	E258243	180℃																	
3	Base	Fog Tin OR EQUIVALENT	NA	NA																	
4	SOLDER	Sn99.3-Cu0.7 OR EQUIVALENT	NA	NA																	
*NA:NOT APPLICABLE.																					

文件编号 File Number	SRD-WI-15603	版本号 Version Number	A	页码 page	2/8
---------------------	--------------	-----------------------	---	------------	-----


5、产品包装 Packaging

1) 载带包装示意图 Tape packing diagram




ITEM	W	A0	B0	K0	P	E	F	D0	P1	P2	T
DIM	24.00	12.0	10.7	5.20	16.00	11.50	1.75	1.50	4.00	2.00	0.35
TOLE	±0.3	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	+0.1	±0.1	±0.1	±0.05

2) 卷盘尺寸 REEL DIMENSION(mm)




3) 卷盘包装示意图 Tape packing diagram




4) 剥离强度要求Peeling required

- ①F 力大小：20~100g；
- ②面带剥离角度：165°~180°。



5) 包装数量 Packing quantity



项目 (Project)	数量 (PCS)	尺寸规格 (Size:mm)
盘(Reel)	500	13"
内盒 (Inner box)	1000	340mm*340mm*65mm
外箱 (Out box)	3000	360mm*360mm*235mm

文件编号 File Number	SRD-WI-15603	版本号 Version Number	A	页码 page	5/8
6.RELIABILITY TEST METHOD					
MECHANICAL					
TEST ITEM	SPECIFICATION	TEST DETAILS			
Substrate bending	$\Delta L/L_0 \leq \pm 5\%$ There shall be no mechanical damage or electrical damage.	The sample shall be soldered onto the printed circuit board in figure 1 and a load applied until the figure in the arrow direction is made approximately 3mm.(keep time 30 seconds) PCB dimension shall the page 7/9 F(Pressurization)  figure-1			
Vibration	$\Delta L/L_0 \leq \pm 5\%$ There shall be no mechanical damage.	The sample shall be soldered onto the printed circuit board and when a vibration having an amplitude of 1.52mm and a frequency of from 10 to 55Hz/1 minute repeated should be applied to the 3 directions (X,Y,Z) for 2 hours each. (A total of 6 hours)			
Solderability	New solder More than 90%	Flux (rosin, isopropyl alcohol{JIS-K-1522}) shall be coated over the whole of the sample before hard, the sample shall then be preheated for about 2 minutes in a temperature of 130~150℃ and after it has been immersed to a depth 0.5mm below for 3±0.2 seconds fully in molten solder M705 with a temperature of 245±2℃. More than 90% of the electrode sections shall be covered with new solder smoothly when the sample is taken out of the solder bath.			

文件编号 File Number	SRD-WI-15603	版本号 Version Number	A	页码 page	6/8
MECHANICAL					
TEST ITEM	SPECIFICATION				
Resistance to Soldering heat (reflow soldering)	There shall be no damage or problems.	Temperature profile of reflow soldering The specimen shall be passed through the reflow oven with the condition shown in the above profile for 1 time. The specimen shall be stored at standard atmospheric conditions for 1 hour, after which the measurement shall be made.			
ELECTRICAL					
TEST ITEM	SPECIFICATION	TEST DETAILS			
Insulation resistance	There shall be no other damage or problems.	DC 100V voltage shall be applied across this sample of top surface and the terminal.			
		The insulation resistance shall be more than 1 × 10 ⁸ Ω.			
Dielectric withstand voltage	There shall be no other damage or problems.	AC 100V voltage shall be applied for 1 minute across the top surface and the terminal of this sample			
Temperature characteristics	ΔL/L20℃ ≒ ±10% 0~2000 ppm/℃	The test shall be performed after the sample has stabilized in an ambient temperature of - 40 to + 125℃ ,and the value calculated based on the value applicable in a normal temperature and normal humidity shall be ΔL/L 20℃ ≒ ± 10%.			

文件编号 File Number	SRD-WI-15603	版本号 Version Number	A	页码 page	7/8
---------------------	--------------	-----------------------	---	------------	-----

ENVIROMENT CHARACTERISTICS																	
TEST ITEM	SPECIFICATION																
High temperature storage	△L/Lo≦±5% There shall be no mechanical damage.	The sample shall be left for 500hours in an atmospere with a temperature of 125±2℃ and a normal humidity. Upon completion of the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.															
Low temperature storage	△L/Lo≦±5% There shall be no mechanical damage.	The sample shall be left for 500 hours in an atmosphere with a temperature of -40±3℃. Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.															
Change of temperature	△L/Lo≦±5% There shall be no other dama-ge of problems	The sample shall be subject to 5 continuos cycles, such as shown in the table 2 below and then it shall be subjected to standard stmospheric conditions for 1 hour, after which measurement shall be made. table 2 <table><tr><td></td><td>Temperature</td><td>Duration</td></tr><tr><td>1</td><td>－40±3℃ (Thermostat No.1)</td><td>10 min.</td></tr><tr><td>2</td><td>Standard atmospheric</td><td>5 sec. or less No.1→No.2</td></tr><tr><td>3</td><td>125±2℃ (Thermostat No.2)</td><td>30 min.</td></tr><tr><td>4</td><td>Standard atmospheric</td><td>5 sec. or less No.2→No.1</td></tr></table>		Temperature	Duration	1	－40±3℃ (Thermostat No.1)	10 min.	2	Standard atmospheric	5 sec. or less No.1→No.2	3	125±2℃ (Thermostat No.2)	30 min.	4	Standard atmospheric	5 sec. or less No.2→No.1
	Temperature	Duration															
1	－40±3℃ (Thermostat No.1)	10 min.															
2	Standard atmospheric	5 sec. or less No.1→No.2															
3	125±2℃ (Thermostat No.2)	30 min.															
4	Standard atmospheric	5 sec. or less No.2→No.1															
Moisutire storage	△L/Lo≦±5% There shall be no mechanical damage.	The sample shall be left for 500 hours in a temperature of 40±2℃ and a humidity(RH) of 90～95%. Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity more than 1 hour.															

Test conditions:
The sample shall be reflow soldered onto the printed circuit board in every test.

文件编号 File Number	SRD-WI-15603	版本号 Version Number	A	页码 page	8/8
8、注意事项 Note					
①本承认书保证我司产品作为一个单体时的质量情况。当我司产品被安装到贵司产品上时，请保证贵司的产品已根据贵司的规范进行了有效评估和确认。 This product specification guarantees the quality of our product as a single unit. Please make sure that your product is evaluated and confirmed against your specifications when our product is mounted to your product. ②如果贵司对我司产品的使用已超过了本承认书所界定的产品功能，那么对于由此引发的失效，我司将不予保证。 We cannot warrant against failure caused by any use of our product that deviates from the intended use as described in this product specification. ③为了保持终端电极的焊接性，并使包装材料保持良好状态，必须控制储存区的温度和湿度。 To maintain the solderability of terminal electrodes and to keep the packing material in good condition, temperature and humidity in the storage area should be controlled. ※建议的条件：-10 ~ +40℃，30~70%RH。 Recommended conditions: -10 ~ +40℃，30~70%RH. ※储存超过六个月的，应在实际使用前进行焊接检验。 In case of storage over 6 months, solderability shall be checked before actual usage. ※即使在理想的储存条件下，产品的可焊性也随着时间的推移而降低。因此，产品应从交货时算起，建议8个月之内使用完。 Even under ideal storage conditions, the weldability of the product decreases over time. therefore, the product should be From the time of delivery, it is recommended that it be used within 8 months. ④本承认书在客户收到30 天之内，必须签章返回，逾期视为默认。 The Specification Approval should be sent back to the supplier with customer's chop on it within 30 days after receiving it, or we will take it as approved by customer's automatically. ⑤如有特殊规格要求，请事前联络我司技术部人员。 In case of special specifications please contact our technical department prior staff.					