






技术指标(Technical Index):


- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):200V DC/AC(rms).
- 3.额定电流(Rated current):2.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 25\text{m}\Omega$.
- 5.耐压值(Withstanding voltage):500V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B
APH2.0-2A-12	2	2.0	6.0
APH2.0-3A-12	3	4.0	8.0
APH2.0-4A-12	4	6.0	10.0
APH2.0-5A-12	5	8.0	12.0
APH2.0-6A-12	6	10.0	14.0
APH2.0-7A-12	7	12.0	16.0
APH2.0-8A-12	8	14.0	18.0
APH2.0-9A-12	9	16.0	20.0
APH2.0-10A-12	10	18.0	22.0
APH2.0-11A-12	11	20.0	24.0
APH2.0-12A-12	12	22.0	26.0
APH2.0-13A-12	13	24.0	28.0
APH2.0-14A-12	14	26.0	30.0
APH2.0-15A-12	15	28.0	32.0
APH2.0-16A-12	16	30.0	34.0
APH2.0-17A-12	17	32.0	36.0
APH2.0-18A-12	18	34.0	38.0
APH2.0-19A-12	19	36.0	40.0
APH2.0-20A-12	20	38.0	42.0


序号	品名	材质			
①	PH2.0直针WTB胶芯	LCP UL94V-0 本色			
②	PH2.0直针WTB端子	铜合金／表面镀锡			
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.		TITLE:	
X.X±0.20		APH2.0-NA-12		PH2.0直针WTB	
X.XX±0.10		DESIGN: Ethan		MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		SCALE SHEET	
MATERILA	— — —	APPD: Ava		①	N:A 1/2
FINISH	— — —				



9. 纸箱分小、中、标准型3种规格型号:装箱为整箱(左下包装量)采用标准型纸箱包装,未达到整箱数量以产品量适当采用小型或中型纸箱包装。



OKT (2.0mm pitch)	W	PCS/RELL	RELL/CARTON	SUM(PCS)
2	24	500	10	5000
3				
4				
5				
6				
7	32	500	8	4000
8				
9	44	500	6	3000
10				
11				
12				
13				
14	56	500	5	2500
15				
16				
17				
18				
19				
20				



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.±0.50	±1°	PART NO.		TITLE:		
X.X±0.20		APH2.0-NA-12		PH2.0直针WTB		
X.XX±0.10		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm	CHED: Olivia				
MATERILA	— — —	APPD: Ava			SCALE	SHEET
FINISH	— — —				N:A	2/2