





技术指标(Technical Index):






- 1.温度范围(Temperature range): $-40^{\circ}\text{C}\sim+125^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V,AC.
- 3.额定电流(Rated current):3.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Withstanding voltage):1000V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B
AHA2.54-2A-22	2	2.5	7.5
AHA2.54-3A-22	3	5.0	10.0
AHA2.54-4A-22	4	7.5	12.5
AHA2.54-5A-22	5	10.0	15.0
AHA2.54-6A-22	6	12.5	17.5
AHA2.54-7A-22	7	15.0	20.0
AHA2.54-8A-22	8	17.5	22.5
AHA2.54-9A-22	9	20.0	25.0
AHA2.54-10A-22	10	22.5	27.5
AHA2.54-11A-22	11	25.0	30.0
AHA2.54-12A-22	12	27.5	32.5
AHA2.54-13A-22	13	30.0	35.0
AHA2.54-14A-22	14	32.5	37.5
AHA2.54-15A-22	15	35.0	40.0
AHA2.54-16A-22	16	37.5	42.5

序号	品名	材质		
①	HA2.5弯针WTB胶芯	LCP UL94V-0 本色		
②	HA2.5弯针WTB端子	铜合金/表面镀锡		
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.±0.50	±1°	PART NO.	TITLE:	
X.X±0.20		HA2.54-NA-22	HA2.5弯针WTB	
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olivia		
MATERILA	— — —	APPD: Ava		
FINISH	— — —		SCALE	SHEET
			N:A	1/2



CKT (2.5mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	24	350	10	3500
3				
4				
5				
6	32	350	8	2800
7				
8				
9				
10	44	350	6	2100
11				
12				
13				
14	56	350	5	1750
15				
16				



纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Hight (CM)	7.5	15	32

- NOTE(注):
- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$. (10片孔距累积公差 $\pm 0.2\text{mm}$.)
 - 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm. (载带拱/弧形MAX:1/100mm.)
 - 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS. (所有的尺寸要满足协会EIA-481规范.)
 - 4.MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING. (载带材料: 透明防静电 PS, 冷封.)
 - 5.THICKNESS: $0.50 \pm 0.05\text{mm}$. (载带厚度: $0.50 \pm 0.05\text{mm}$.)
 - 6.PACKING LENGTH PER REEL: 5.952 METERS. (每卷包装长度: 5.952米.)
 - 7.COMPONENT LOAD PER REEL: 350 PCS. (每卷包装数量: 350只, 前后各空11只.)
 - 8.纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及保丽龙填充.
 - 9.纸箱分小、中、标准型3种规格型号: 装箱为整箱(在下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装.

CKT (2.5mm pitch)	B0	W	F	s
2	7.80	24	11.50	
3	10.30			
4	12.80			
5	15.30			
6	17.80	32	14.20 ± 0.10	28.40
7	20.30			
8	22.80			
9	25.30			
10	27.80	44	20.20 ± 0.10	40.40
11	30.30			
12	32.80			
13	35.30			
14	37.80	56	26.2 ± 0.10	52.40
15	40.30			
16	42.80			

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X. ± 0.50	$\pm 1^\circ$	PART NO. AHA2.54-NA-22	TITLE: HA2.5 4针WTB		
X.X ± 0.25					
X.XX ± 0.15					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERIAL	---	CHED: Olivia		SCALE	SHEET
FINISH	---	APPD: Ava		N:A	2/2