

SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
Contact Material: Brass
Insrlator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PA6T
Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds
(260 $^{\circ}$ Cfor10seconds)

P-Z/N	P-ZIN	DIM.A	DIM.B
XY-IDC2.54-2*3P-Z	2*3	5.08	7.62
XY-IDC2.54-2*4P-Z	2*4	7.62	10.16
XY-IDC2.54-2*5P-Z	2*5	10.16	12.70
XY-IDC2.54-2*6P-Z	2*6	12.70	15.24
XY-IDC2.54-2*7P-Z	2*7	15.24	17.78
XY-IDC2.54-2*8P-Z	2*8	17.78	20.32
XY-IDC2.54-2*9P-Z	2*9	20.32	22.86
XY-IDC2.54-2*10P-Z	2*10	22.86	25.40
XY-IDC2.54-2*12P-Z	2*12	27.94	30.48
XY-IDC2.54-2*13P-Z	2*13	30.48	33.02
XY-IDC2.54-2*14P-Z	2*14	33.02	35.56
XY-IDC2.54-2*15P-Z	2*15	35.56	38.10
XY-IDC2.54-2*16P-Z	2*16	38.10	40.64
XY-IDC2.54-2*17P-Z	2*17	40.64	43.18
XY-IDC2.54-2*18P-Z	2*18	43.18	45.72
XY-IDC2.54-2*20P-Z	2*20	48.26	50.80
XY-IDC2.54-2*22P-Z	2*22	53.34	55.88
XY-IDC2.54-2*25P-Z	2*25	60.96	63.50
XY-IDC2.54-2*30P-Z	2*30	73.66	76.20
XY-IDC2.54-2*32P-Z	2*32	78.74	81.28

RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)