


**Features**

- Super Low Gate Charge
- Green Device Available
- Fast Switching Speed
- Advanced high cell density Trench technology


Bvdss**60V****Rdson****28mΩ****ID****20A****Application**

- DC-DC Converters
- Power management functions
- Synchronous-rectification applications


RoHS

Package

Marking and pin assignment



PDFN3x3-8L top view



Schematic diagram

Package Marking and Ordering Information

Device Marking	Device	Device Package	Quantity
20N06	20N06D	PDFN3x3-8L	5000

Absolute Maximum Ratings ($T_C=25^{\circ}\text{C}$ unless otherwise specified)

Parameter		Symbol	Limit	Unit
Drain-Source Voltage		V_{DS}	60	V
Gate-Source Voltage		V_{GS}	± 20	V
Continuous Drain Current, $V_{GS}@10V^1$	$T_C=25^{\circ}\text{C}$	I_D	20	A
	$T_C=70^{\circ}\text{C}$		10	A
Pulsed Drain Current ²		I_{DM}	46	A
Single Pulsed Avalanche Energy ³		EAS	25.5	mJ
Avalanche Current		I_{AS}	20	A
Total Power Dissipation ⁴		P_D	34.5	W
Operating Junction Temperature Range		T_J	-55 ~ 150	$^{\circ}\text{C}$
Storage Temperature Range		T_{STG}	-55 ~ 150	$^{\circ}\text{C}$



Thermal Resistance Ratings

Parameter	Symbol	Typ.	Max.	Unit
Thermal Resistance Junction-to-Case ¹	$R_{\theta JC}$	--	--	$^{\circ}\text{C/W}$
Thermal Resistance Junction-to-Ambient ¹	$R_{\theta JA}$	--	62	$^{\circ}\text{C/W}$

Ordering Information

Ordering Number	Package	Pin Assignment			Packing
Halogen Free		G	D	S	
HL20N06D	PDFN3x3-8L	4	5,6,7,8	1,2,3	Tape Reel

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise specified)

Parameter	Symbol	Condition	Min	Typ	Max	Unit
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=250\mu A$	60	-	-	V
Drain-Source Leakage Current	I_{DSS}	$V_{DS}=60V, V_{GS}=0V$	-	-	1	μA
Gate-Source Leakage Current	I_{GSS}	$V_{DS}=0V, V_{GS}=\pm 20V$	-	-	± 100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	1	1.6	2.5	V
Static Drain-Source On-Resistance ³	$R_{DS(on)}$	$V_{GS}=10V, I_D=5A$	-	28	40	m Ω
		$V_{GS}=4.5V, I_D=3A$	-	36	50	
Gate Resistance	R_g	$V_{DS}=0V, V_{GS}=0V, f=1\text{MHz}$	-	-	-	Ω
Input Capacitance	C_{iss}	$V_{DS}=25V, V_{GS}=0V,$ $f=1\text{MHz}$	-	1148	-	pF
Output Capacitance	C_{oss}		-	59	-	
Reverse Transfer Capacitance	C_{rss}		-	49	-	
Total Gate Charge	Q_g	$V_{DS}=30V, V_{GS}=10V,$ $I_D=2.5A$	-	20.5	-	nC
Gate-Source Charge	Q_{gs}		-	3.5	-	
Gate-Drain Charge	Q_{gd}		-	5.5	-	
Turn-on Delay Time	$T_{d(on)}$	$V_{GS}=10V, V_{DS}=30V,$ $R_G=1.8\Omega, I_D=5A$	-	7.5	-	nS
Turn-on Rise Time	T_r		-	20	-	
Turn-Off Delay Time	$T_{d(off)}$		-	15	-	
Turn-Off Fall Time	T_f		-	24	-	
Diode Forward Voltage	V_{SD}	$V_{GS}=0V, I_S=1A$	-	-	1.2	V
Continuous Source Current	I_S	$V_G=V_D=0V, \text{Force Current}$	-	-	5	A
Pulsed Source Current	I_{SM}		-	-	20	
Body Diode Reverse Recovery Time	t_{rr}	$I_F=5A, di/dt=100A/\mu s$	-	29	-	ns
Body Diode Reverse Recovery Charge	Q_{rr}		-	43	-	nC

Notes:

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature.
2. EAS condition : $T_J=25^{\circ}\text{C}, V_{DD}=30V, V_G=10V, L=0.5\text{mH}, R_G=25\Omega, I_{AS}=8.7A$.
3. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 0.5\%$.



Typical Performance Characteristics

Figure 1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics






Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Ambient Temperature






Figure 11: Maximum Effective Transient Thermal Impedance, Junction-to-Ambient




Package Mechanical Data PDFN3x3-8L



NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M,1994.
2. ALL DIMNESIONS IN MILLIMETER (ANNGLE IN DEGREE).
3. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH PROTRUSIONS OR GATE BURRS.

DIM.	MILLIMETER		
	MIN.	NOM.	MAX.
A	0.70	0.75	0.80
b	0.25	0.30	0.35
c	0.10	0.20	0.25
D	3.00	3.15	3.25
D1	2.95	3.05	3.15
D2	2.39	2.49	2.59
E	3.20	3.30	3.40
E1	2.95	3.05	3.15
E2	1.70	1.80	1.90
e	0.65 BSC		
H	0.30	0.40	0.50
L	0.25	0.40	0.50
a	---	---	15°



DIMENSIONS:MILLIMETERS



Important Notice and Disclaimer

HL Microelectronics reserves the right to make changes to this document and its products and specifications at any time without notice.

Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

HL Microelectronics makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, not does HL Microelectronics assume any liability for application assistance or customer product design.

HL Microelectronics does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of HL Microelectronics.

HL Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of HL Microelectronics.