


1.Features

- ESD immunity acc. IEC 61000-4-2
 - ± 30 kV contact discharge
 - ± 30 kV air discharge
- Single-line ESD protection device

2.Pinning information



3.1Absolute Maximum Ratings GSOT03

Parameter	Symbol	Symbol	Value	Units
Peak pulse current	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	I_{PPM}	30	A
Peak pulse power	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	P_{PP}	369	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	±30	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		±30	kV
Junction Temperature	Junction temperature	T_J	-40 to 125	°C
Storage temperature		T_{STG}	-55 to 150	°C



3.2 Absolute Maximum Ratings GSOT04

Parameter	Symbol	Symbol	Value	Units
Peak pulse current	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	I_{PPM}	30	A
Peak pulse power	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	P_{PP}	429	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	± 30	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		± 30	kV
Junction Temperature	Junction temperature	T_J	-40 to 125	$^{\circ}C$
Storage temperature		T_{STG}	-55 to 150	$^{\circ}C$

3.3 Absolute Maximum Ratings GSOT05

Parameter	Symbol	Symbol	Value	Units
Peak pulse current	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	I_{PPM}	30	A
Peak pulse power	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	P_{PP}	480	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	± 30	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		± 30	kV
Junction Temperature	Junction temperature	T_J	-40 to 125	$^{\circ}C$
Storage temperature		T_{STG}	-55 to 150	$^{\circ}C$

3.4 Absolute Maximum Ratings GSOT08

Parameter	Symbol	Symbol	Value	Units
Peak pulse current	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	I_{PPM}	18	A
Peak pulse power	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	P_{PP}	345	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	± 30	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		± 30	kV
Junction Temperature	Junction temperature	T_J	-40 to 125	$^{\circ}C$
Storage temperature		T_{STG}	-55 to 150	$^{\circ}C$



3.5 Absolute Maximum Ratings GSOT12

Parameter	Symbol	Symbol	Value	Units
Peak pulse current	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	I_{PPM}	12	A
Peak pulse power	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	P_{PP}	312	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	± 30	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		± 30	kV
Junction Temperature	Junction temperature	T_J	-40 to 125	$^{\circ}C$
Storage temperature		T_{STG}	-55 to 150	$^{\circ}C$

3.6 Absolute Maximum Ratings GSOT15

Parameter	Symbol	Symbol	Value	Units
Peak pulse current	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	I_{PPM}	8	A
Peak pulse power	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	P_{PP}	230	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	± 30	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		± 30	kV
Junction Temperature	Junction temperature	T_J	-40 to 125	$^{\circ}C$
Storage temperature		T_{STG}	-55 to 150	$^{\circ}C$

3.7 Absolute Maximum Ratings GSOT24

Parameter	Symbol	Symbol	Value	Units
Peak pulse current	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	I_{PPM}	5	A
Peak pulse power	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	P_{PP}	235	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	± 30	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		± 30	kV
Junction Temperature	Junction temperature	T_J	-40 to 125	$^{\circ}C$
Storage temperature		T_{STG}	-55 to 150	$^{\circ}C$





3.8 Absolute Maximum Ratings GSOT36

Parameter	Symbol	Symbol	Value	Units
Peak pulse current	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	I_{PPM}	3.5	A
Peak pulse power	Pin 3 to 1 acc. IEC 61000-4-5, $t_p=8/20\mu s$; single shot	P_{PP}	248	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	± 30	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		± 30	kV
Junction Temperature	Junction temperature	T_J	-40 to 125	$^{\circ}C$
Storage temperature		T_{STG}	-55 to 150	$^{\circ}C$



4. BiAs-MODE (1-line Bidirectional Asymmetrical protection mode)

With the GSOTxx one signal- or data-lines (L1) can be protected against voltage transients. With pin 1 connected to ground and pin 3 connected to a signal- or data-line which has to be protected. As long as the voltage level on the data- or signal-line is between 0 V (ground level) and the specified maximum reverse working voltage (V_{RWM}) the protection diode between pin 1 and pin 3 offers a high isolation to the ground line. The protection device behaves like an open switch. As soon as any positive transient voltage signal exceeds the breakdown voltage level of the protection diode, the diode becomes conductive and shorts the transient current to ground. Now the protection device behaves like a closed switch. The clamping voltage (V_C) is defined by the breakdown voltage (V_{BR}) level plus the voltage drop at the series impedance (resistance and inductance) of the protection diode. Any negative transient signal will be clamped accordingly. The negative transient current is flowing in the forward direction through the protection diode. The low forward voltage (V_F) clamps the negative transient close to the ground level. Due to the different clamping levels in forward and reverse direction the GSOTxx clamping behavior is Bidirectional and Asymmetrical (BiAs).





5.1 Electrical Characteristics GSOT03 ($T_{amb}=25\text{ }^{\circ}\text{C}$)

between pin 3 and pin 1

Parameter	Symbol	Test Conditions/Remarks	Min	Typ	Max	Units
Protection paths	$N_{channel}$	Number of lines which can be protected			1	lines
Reverse stand-off voltage	V_{RWM}	Max. reverse working voltage			3.3	V
Reverse voltage	V_R	at $I_R=100\mu\text{A}$	3.3			V
Reverse current	I_R	at $V_R=3.3\text{V}$			100	μA
Reverse breakdown voltage	V_{BR}	at $I_R=1\text{mA}$	4	4.6	5.5	V
Reverse clamping voltage	V_C	at $I_{PP}=1\text{A}$		5.7	7.5	V
		at $I_{PP}=I_{PPM}=30\text{ A}$		10	12.3	V
Forward clamping voltage	V_F	at $I_{PP}=1\text{A}$		1	1.2	V
		at $I_{PP}=I_{PPM}=30\text{ A}$		4.5		V
Capacitance	C_D	at $V_R=0\text{V}$, $f=1\text{MHz}$		420	600	pF
		at $V_R=1.6\text{V}$, $f=1\text{MHz}$		260		pF

5.2 Electrical Characteristics GSOT04 ($T_{amb}=25\text{ }^{\circ}\text{C}$)

between pin 3 and pin 1

Parameter	Symbol	Test Conditions/Remarks	Min	Typ	Max	Units
Protection paths	$N_{channel}$	Number of lines which can be protected			1	lines
Reverse stand-off voltage	V_{RWM}	Max. reverse working voltage			4	V
Reverse voltage	V_R	at $I_R=20\mu\text{A}$	4			V
Reverse current	I_R	at $V_R=4\text{V}$			20	μA
Reverse breakdown voltage	V_{BR}	at $I_R=1\text{mA}$	5	6.1	7	V
Reverse clamping voltage	V_C	at $I_{PP}=1\text{A}$		7.5	9	V
		at $I_{PP}=I_{PPM}=30\text{ A}$		11.2	14.3	V
Forward clamping voltage	V_F	at $I_{PP}=1\text{A}$		1	1.2	V
		at $I_{PP}=I_{PPM}=30\text{ A}$		4.5		V
Capacitance	C_D	at $V_R=0\text{V}$, $f=1\text{MHz}$		310	450	pF
		at $V_R=2\text{V}$, $f=1\text{MHz}$		200		pF



5.3 Electrical Characteristics GSOT05 ($T_{amb}=25\text{ }^{\circ}\text{C}$)

between pin 3 and pin 1

Parameter	Symbol	Test Conditions/Remarks	Min	Typ	Max	Units
Protection paths	$N_{channel}$	Number of lines which can be protected			1	lines
Reverse stand-off voltage	V_{RWM}	Max. reverse working voltage			5	V
Reverse voltage	V_R	at $I_R=10\mu\text{A}$	5			V
Reverse current	I_R	at $V_R=5\text{V}$			10	μA
Reverse breakdown voltage	V_{BR}	at $I_R=1\text{mA}$	6	6.8	8	V
Reverse clamping voltage	V_C	at $I_{PP}=1\text{A}$		7	8.7	V
		at $I_{PP}=I_{PPM}=30\text{ A}$		12	16	V
Forward clamping voltage	V_F	at $I_{PP}=1\text{A}$		1	1.2	V
		at $I_{PP}=I_{PPM}=30\text{ A}$		4.5		V
Capacitance	C_D	at $V_R=0\text{V}$, $f=1\text{MHz}$		260	350	pF
		at $V_R=2.5\text{V}$, $f=1\text{MHz}$		150		pF

5.4 Electrical Characteristics GSOT08 ($T_{amb}=25\text{ }^{\circ}\text{C}$)

between pin 3 and pin 1

Parameter	Symbol	Test Conditions/Remarks	Min	Typ	Max	Units
Protection paths	$N_{channel}$	Number of lines which can be protected			1	lines
Reverse stand-off voltage	V_{RWM}	Max. reverse working voltage			8	V
Reverse voltage	V_R	at $I_R=5\mu\text{A}$	8			V
Reverse current	I_R	at $V_R=8\text{V}$			5	μA
Reverse breakdown voltage	V_{BR}	at $I_R=1\text{mA}$	9	10	11	V
Reverse clamping voltage	V_C	at $I_{PP}=1\text{A}$		10.7	13	V
		at $I_{PP}=I_{PPM}=18\text{A}$		15.2	19.2	V
Forward clamping voltage	V_F	at $I_{PP}=1\text{A}$		1	1.2	V
		at $I_{PP}=I_{PPM}=18\text{A}$		3		V
Capacitance	C_D	at $V_R=0\text{V}$, $f=1\text{MHz}$		160	250	pF
		at $V_R=4\text{V}$, $f=1\text{MHz}$		80		pF



5.5 Electrical Characteristics GSOT12 ($T_{amb}=25\text{ }^{\circ}\text{C}$)

between pin 3 and pin 1

Parameter	Symbol	Test Conditions/Remarks	Min	Typ	Max	Units
Protection paths	$N_{channel}$	Number of lines which can be protected			1	lines
Reverse stand-off voltage	V_{RWM}	Max. reverse working voltage			12	V
Reverse voltage	V_R	at $I_R=1\mu\text{A}$	12			V
Reverse current	I_R	at $V_R=12\text{V}$			1	μA
Reverse breakdown voltage	V_{BR}	at $I_R=1\text{mA}$	13.5	15	16.5	V
Reverse clamping voltage	V_C	at $I_{PP}=1\text{A}$		15.4	18.7	V
		at $I_{PP}=I_{PPM}=12\text{A}$		21.2	26	V
Forward clamping voltage	V_F	at $I_{PP}=1\text{A}$		1	1.2	V
		at $I_{PP}=I_{PPM}=12\text{A}$		2.2		V
Capacitance	C_D	at $V_R=0\text{V}$, $f=1\text{MHz}$		115	150	pF
		at $V_R=6\text{V}$, $f=1\text{MHz}$		50		pF

5.6 Electrical Characteristics GSOT15 ($T_{amb}=25\text{ }^{\circ}\text{C}$)

between pin 3 and pin 1

Parameter	Symbol	Test Conditions/Remarks	Min	Typ	Max	Units
Protection paths	$N_{channel}$	Number of lines which can be protected			1	lines
Reverse stand-off voltage	V_{RWM}	Max. reverse working voltage			15	V
Reverse voltage	V_R	at $I_R=1\mu\text{A}$	15			V
Reverse current	I_R	at $V_R=15\text{V}$			1	μA
Reverse breakdown voltage	V_{BR}	at $I_R=1\text{mA}$	16.5	18	20	V
Reverse clamping voltage	V_C	at $I_{PP}=1\text{A}$		19.4	23.5	V
		at $I_{PP}=I_{PPM}=8\text{A}$		24.8	28.8	V
Forward clamping voltage	V_F	at $I_{PP}=1\text{A}$		1	1.2	V
		at $I_{PP}=I_{PPM}=8\text{A}$		1.8		V
Capacitance	C_D	at $V_R=0\text{V}$, $f=1\text{MHz}$		90	120	pF
		at $V_R=7.5\text{V}$, $f=1\text{MHz}$		35		pF



5.7 Electrical Characteristics GSOT24 ($T_{amb}=25\text{ }^{\circ}\text{C}$)

between pin 3 and pin 1

Parameter	Symbol	Test Conditions/Remarks	Min	Typ	Max	Units
Protection paths	$N_{channel}$	Number of lines which can be protected			1	lines
Reverse stand-off voltage	V_{RWM}	Max. reverse working voltage			24	V
Reverse voltage	V_R	at $I_R=1\mu\text{A}$	24			V
Reverse current	I_R	at $V_R=24\text{V}$			1	μA
Reverse breakdown voltage	V_{BR}	at $I_R=1\text{mA}$	27	30	33	V
Reverse clamping voltage	V_C	at $I_{PP}=1\text{A}$		34	41	V
		at $I_{PP}=I_{PPM}=5\text{A}$		41	47	V
Forward clamping voltage	V_F	at $I_{PP}=1\text{A}$		1	1.2	V
		at $I_{PP}=I_{PPM}=5\text{A}$		1.4		V
Capacitance	C_D	at $V_R=0\text{V}$, $f=1\text{MHz}$		65	80	pF
		at $V_R=12\text{V}$, $f=1\text{MHz}$		20		pF

5.8 Electrical Characteristics GSOT36 ($T_{amb}=25\text{ }^{\circ}\text{C}$)

between pin 3 and pin 1

Parameter	Symbol	Test Conditions/Remarks	Min	Typ	Max	Units
Protection paths	$N_{channel}$	Number of lines which can be protected			1	lines
Reverse stand-off voltage	V_{RWM}	Max. reverse working voltage			36	V
Reverse voltage	V_R	at $I_R=1\mu\text{A}$	36			V
Reverse current	I_R	at $V_R=36\text{V}$			1	μA
Reverse breakdown voltage	V_{BR}	at $I_R=1\text{mA}$	39	43	47	V
Reverse clamping voltage	V_C	at $I_{PP}=1\text{A}$		49	60	V
		at $I_{PP}=I_{PPM}=3.5\text{A}$		59	71	V
Forward clamping voltage	V_F	at $I_{PP}=1\text{A}$		1	1.2	V
		at $I_{PP}=I_{PPM}=3.5\text{A}$		1.3		V
Capacitance	C_D	at $V_R=0\text{V}$, $f=1\text{MHz}$		52	65	pF
		at $V_R=18\text{V}$, $f=1\text{MHz}$		12		pF



6.1 Typical characteristic




Figure 1: Typical Forward Current I_F vs. Forward Voltage V_F




Figure 2: ESD Discharge Current Waveform According to IEC 61000-4-2 (330 Ω / 150 pF)




Figure 3: Typical Reverse Voltage V_R vs. Reverse Current I_R




Figure 4: 8/20 μ s Peak Pulse Current Waveform According to IEC 61000-4-5




Figure 5: Typical Reverse Voltage V_R vs. Reverse Current I_R




Figure 6: Typical Clamping Voltage vs. Peak Pulse Current



6.2 Typical characteristic




Figure 7: Typical Clamping Voltage vs. Peak Pulse Current




Figure 8: Typical Peak Clamping Voltage vs. Peak Pulse Current




Figure 9: Typical Peak Clamping Voltage vs. Peak Pulse Current





Figure 10: Typical Capacitance vs. Reverse Voltage



7.SOT-23 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	B	b_p	C	D	E	H_E	A_1	L_p
Min	0.95	1.78	0.35	0.08	2.70	1.20	2.20	0.013	0.20
Max	1.40	2.04	0.50	0.19	3.10	1.65	3.00	0.100	0.50



8.Ordering information



yww: Batch Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW GSOT03-E3-08	03	SOT-23	3000	Tape and reel
UMW GSOT04-E3-08	04	SOT-23	3000	Tape and reel
UMW GSOT05-E3-08	05	SOT-23	3000	Tape and reel
UMW GSOT08-E3-08	08	SOT-23	3000	Tape and reel
UMW GSOT12-E3-08	12	SOT-23	3000	Tape and reel
UMW GSOT15-E3-08	15	SOT-23	3000	Tape and reel
UMW GSOT24-E3-08	24	SOT-23	3000	Tape and reel
UMW GSOT36-E3-08	36	SOT-23	3000	Tape and reel



9.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.